

MNR201610 Series

Wire Wound SMD Power Inductors

FEATURES

- Magnetic-resin shielded construction reduces buzz noise to ultra-low levels
- Metallization on ferrite core results in excellent shock resistance and damage-free durability
- Closed magnetic circuit design reduces leakage flux and Electro Magnetic Interference (EMI)
- 30% higher current rating than conventional inductors of equal size
- Takes up less PCB real estate and save more power
- Operate temperature range -40° C $\sim +125^{\circ}$ C (Including self temp. rise)
- RoHS compliant



APPLICATIONS

- Smart phone, smart TV, set top box, notebook
- Car navigation systems, telecomm base stations
- VR, AR
- LED lighting


Explanation of Part Number

MNR 201610T 1R0 M T


1 2 3 4 5 6


- ♦ 1:Product Series:Wire Wound SMD Power Inductors
- ♦ 2:Dimensions:
- ♦ 3: Feature Type:T Type
- ◆ 4: Initial inductance value: 1R0 = 1.0uH
- ◆ 5: Tolerance of Inductance:M:+/-20%, N:+/-30%
- ♦ 6:Packing:Tape Carrier Package

Dimensions: [mm]









Recommended Land Pattern

Series	A	В	С	D	Е	F	а Тур.	b Typ.	с Тур.
MNR201610T	2.0±0.3	1.6±0.3	1.05 Max	1.2±0.2	0.6±0.2	0.8±0.2	0.70	0.70	1.70




Electrical Characteristics List

MNR201610 Series

Part Number	Inductance	DC Res	istance	Isat(A)		Irms(A)	
Fart Number	100KHz/1.0V	Max.	Тур.	Max.	Тур.	Max.	Тур.
Units	(uH)	Ω	Ω	A	A	A	A
MNR201610TR22NT	0.22±30%	0.040	0.033	3.70	4.10	2.80	3.10
MNR201610TR24NT	0.24±30%	0.040	0.033	3.70	4.10	2.80	3.10
MNR201610TR33NT	0.33±30%	0.048	0.043	3.00	3.70	2.40	2.90
MNR201610TR47NT	0.47±30%	0.060	0.052	2.30	2.85	2.30	2.60
MNR201610TR68NT	0.68±30%	0.076	0.068	1.95	2.45	2.00	2.20
MNR201610T1R0MT	1.0±20%	0.114	0.104	1.65	1.85	1.45	1.60
MNR201610T1R5MT	1.5±20%	0.174	0.164	1.35	1.65	1.10	1.20
MNR201610T2R2MT	2.2±20%	0.265	0.232	1.20	1.45	1.05	1.15
MNR201610T3R3MT	3.3±20%	0.345	0.328	1.00	1.20	0.85	0.95
MNR201610T4R7MT	4.7±20%	0.480	0.430	0.75	0.90	0.70	0.80
MNR201610T6R8MT	6.8±20%	0.800	0.715	0.70	0.85	0.55	0.60
MNR201610T8R2MT	8.2±20%	0.940	0.818	0.68	0.78	0.53	0.60
MNR201610T100MT	10±20%	1.000	0.930	0.65	0.70	0.50	0.60

^{%1:} All test data is referenced to 20°C ambient;

Structure



NO.	Components	Material
1	Core	Ni-Zn Ferrite
2	Wire	Polyurethane system enameled copper wire
3	Magnetic Glue	Epoxy resin and magnetic powder
4	Electrodes	AgNiSn or FeNiCu + Sn Alloy

^{%2:} Rated current: Isat or Irms, whichever is smaller;

[%]*3: Isat: DC current at which the inductance drops approximate 30% from its value without current;

[%]*4: Irms: DC current that causes the temperature rise (\triangle T =40°C) from 20°C ambient.



Reliability Test

TEST ITEM	SPECIFICATION	TEST CONDITION		
Withstanding voltage test	After test, inductors shall have no evidence of electrical and mechanical damage.	AC voltage of 100v and AC current of 1mA applied between inductor's terminal and core for 3 secs.		
Resistance to soldering heat	 Inductor shall have no eviden of electrical and mechanical damage. Inductance shall not chan more than ±5%. Q shall not change more than 20%. 	a. Temp: 260±5 b. Time: 10±1.0 se		
Solderability test	The terminal shall be at least 95% covered with solder.	After fluxing, the terminal shall be dipped in a melted solder bath at 245 ± 5 °C for 4 ± 1.0 secs.		
High temperature & high humidity test	The anti-erosion quality of the	a. Test conditi 1)Temp.:85°C, R.H.:85% 2)Time:144±2hours b. Measurement method The experimental component should be put a normal condition for 2 hours then to measure again after test		
Salt spray test	surface and the specimen's inductance shall not change from the initial value within ±10%	a. Test conditi 1)Temp.:35±2°C 2)Time:48±2hours 3)Salt solution PH:6.5~7.2 b. Measurement method The experimental component should be put normal condition for 2 hours then to measure again after test		
Vibration test	Inductance shall be within 10% of the initial value. Appearance:no dama	a. Frequency: 10 to 55b. Amplitude: 1.5c. Direction and timX, Y and Z directions for 2 hours each.		





TEST ITEM	SPECIFICATION	TEST CONDITION		
Free fall test	No mechanical damage shall be noticed.	Drop 5 times on a concrete floor from lm the height		
Temperature Cycling test		a. Test conditi 1)Temp.:-55°C,time:30±3min 2)Temp.:+125°C,time: 30±3min 3)Cycles times:12 cycles b. Measurement method The experimental component should be put at normal condition for 2 hours then to measure again after test		
High Temperature resistance test	 Inductance shall be within 10% of the initial value Appearance:No dama 	a. Test conditi 1)Applied rated current 2)Temp.:85℃±2℃ 3)Test time:1000+24/-0H b. Measurement method The experimental component should be put at normal condition for 24 hours then to measure again after test.		
Low temperature resistance test		a. Test conditi 1)Temp.:-55°C±2°C 2)Test time:1000+24/-0H b. Measurement method The experimental component should be put at normal condition for 24 hours then to measure again after test.		

We have suggested the storage period of lead-free product should not over 6 months.



PACKAGING SPECIFICATION:





Type	Α	В	С	G	N	T
8mm	178	20.7±0.8	13±0.4	9	60	10.8

Packaging Quantity:2K/Reel

Re-flowing Profile:

