





### SPECIFICATIONS

Current Rating: 3Amps  
 Insulation Resistance: 1000MΩ Min  
 Contact Resistance: 20mΩ Max  
 Withstanding Voltage: AC 1000V  
 Operation Temperature: -40° to +105°  
 Contact Material: Brass  
 Standard: PA6T  
 Insulator Material: Polyester(UL 94V-0)  
 Contact Plating: Gold Flash  
 Max.Processing Temp: 240°C for 30-60seconds  
 (260°C for 5seconds)

P/N	PIN	DIM.A	DIM.B
PH2.54-01-01PZD	1	0.00	2.54
PH2.54-01-02PZD	2	2.54	5.08
PH2.54-01-03PZD	3	5.08	7.62
PH2.54-01-04PZD	4	7.62	10.16
PH2.54-01-05PZD	5	10.16	12.70
PH2.54-01-06PZD	6	12.70	15.24
PH2.54-01-07PZD	7	15.24	17.78
PH2.54-01-08PZD	8	17.78	20.32
PH2.54-01-09PZD	9	20.32	22.86
.....	.....	.....	.....
PH2.54-01-40PZD	40	(PIN-1)X2.54	(PIN)X2.54



PART NUMBER DESCRIPTION:

PH2.54-01-NPZD

- └ (D=单排; S=双排)
- └ (Z=直脚; W=弯脚)
- └ (PIN数量; 01.....40PIN)
- └ (排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 1xNPin 180度 PC3.0 PA6.0 PB2.5 L11.5 6T
DECIMALS:	ANGLES:		PAR PH2.54-01-NPZD
X.±0.30	X°±5°	DWN	CHKD
X.X±0.20	X.X°±1°	APVD	SCALE N:A UNIT:MM
X.XX±0.10	X.XX°±0.5°	CUSTOMER COPY	SIZE:A4 SHEET:1F1 REV:A