



# DSR0.3A THRU DSR0.3M

Reverse Voltage - 50 to 1000 Volts Forward Current - 0.3 Ampere


## SURFACE MOUNT GENERAL PURPOSE SILICON RECTIFIER

### Features

- ◆ Glass passivated device
- ◆ Ideal for surface mounted applications
- ◆ Low reverse leakage
- ◆ Metallurgically bonded construction
- ◆ High temperature soldering guaranteed:
- ◆ 250°C/10 seconds, 0.375" (9.5mm) lead length, 5 lbs. (2.3kg) tension

### Mechanical Data

Case: JEDEC UOD-123FL molded plastic body  
 Terminals: Solderable per MIL-STD-750, Method 2026A  
 Polarity: Polarity symbol marking on body  
 Mounting Position: Any  
 Weight: 0.0067 ounce, 0.02 grams



Dimensions in inches and (millimeters)

### Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

| Parameter  | SYMBOLS         | DSR0.3A     | DSR0.3B | DSR0.3D | DSR0.3G | DSR0.3J | DSR0.3K | DSR0.3M | UNITS        |
|--|-----------------|-------------|---------|---------|---------|---------|---------|---------|--------------|
| Marking Code   |                 | S03A        | S03B    | S03D    | S03G    | S03J    | S03K    | S03M    |              |
| Maximum repetitive peak reverse voltage  | $V_{RRM}$       | 50          | 100     | 200     | 400     | 600     | 800     | 1000    | V            |
| Maximum RMS voltage  | $V_{RMS}$       | 35          | 70      | 140     | 280     | 420     | 560     | 700     | V            |
| Maximum DC blocking voltage  | $V_{DC}$        | 50          | 100     | 200     | 400     | 600     | 800     | 1000    | V            |
| Maximum average forward rectified current at TL(see fig.1)   | $I_{(AV)}$      | 0.3         |         |         |         |         |         |         | A            |
| Peak forward surge current<br>8.3ms single half sine-wave<br>superimposed on rated load (JEDEC Method) | $I_{FSM}$       | 15.0        |         |         |         |         |         |         | A            |
| Maximum instantaneous forward voltage at 2.0A  | $V_F$           | 1.1         |         |         |         |         |         |         | V            |
| Maximum DC reverse current<br>$T_A=25^\circ C$<br>at rated DC blocking voltage<br>$T_A=125^\circ C$    | $I_R$           | 5.0<br>50   |         |         |         |         |         |         | $\mu A$      |
| Typical junction capacitance (NOTE 1)  | $C_J$           | 4           |         |         |         |         |         |         | pF           |
| Typical thermal resistance (NOTE 2)  | $R_{\theta JA}$ | 220         |         |         |         |         |         |         | $^\circ C/W$ |
| Operating junction temperature range   | $T_J$           | -55 to +150 |         |         |         |         |         |         | $^\circ C$   |
| Storage temperature range  | $T_{STG}$       | -55 to +150 |         |         |         |         |         |         | $^\circ C$   |

- Note:** 1. Averaged over any 20ms period.  
 2. Measured at 1MHz and applied reverse voltage of 4.0V D.C.  
 3. Thermal resistance from junction to ambient at 0.375" (9.5mm) lead length, P.C.B. mounted



# DSR0.3A THRU DSR0.3M

Reverse Voltage - 50 to 1000 Volts Forward Current - 0.3 Ampere

## Typical Characteristics

Characteristic Curves ( $T_A=25^\circ\text{C}$  unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Maximum Non-Repetitive Peak Forward Surge Current




Fig.3 Typical Instantaneous Forward Characteristics





Fig.4 Typical Reverse Characteristics




The curve above is for reference only.



# DSR0.3A THRU DSR0.3M

Reverse Voltage - 50 to 1000 Volts Forward Current - 0.3 Ampere

## Packing information



unit:mm


| Item                     | Symbol | Tolerance | SOD-123FL |
|--------------------------|--------|-----------|-----------|
| Carrier width            | A      | 0.1       | 2.1       |
| Carrier length           | B      | 0.1       | 4.0       |
| Carrier depth            | C      | 0.1       | 1.60      |
| Sprocket hole            | d      | 0.05      | 1.55      |
| 7" Reel outside diameter | D      | 2.0       | 178.00    |
| 7" Reel inner diameter   | D1     | min       | 50.0      |
| Feed hole diameter       | D2     | 0.5       | 13.00     |
| Sprocket hole position   | E      | 0.1       | 1.75      |
| Punch hole position      | F      | 0.1       | 3.50      |
| Punch hole pitch         | P      | 0.1       | 4.00      |
| Sprocket hole pitch      | P0     | 0.1       | 4.00      |
| Embossment center        | P1     | 0.1       | 2.00      |
| Overall tape thickness   | T      | 0.1       | 0.25      |
| Tape width               | W      | 0.3       | 8.15      |
| Reel width               | W1     | 1.0       | 10.5      |

Note: Devices are packed in accordance with EIA standard RS-481-A and specifications listed above.

## Reel packing

| PACKAGE   | REEL SIZE | REEL (pcs) | COMPONENT SPACING (m/m) | BOX (pcs) | INNER BOX (m/m) | REEL DIA, (m/m) | CARTON SIZE (m/m) | CARTON (pcs) | APPROX. GROSS WEIGHT (kg) |
|-----------|-----------|------------|-------------------------|-----------|-----------------|-----------------|-------------------|--------------|---------------------------|
| SOD-123FL | 7"        | 3,000      | 4.0                     | 45,000    | 210*208*203     | 178             | 430*430*235       | 180,000      | 9.0                       |

## Suggested Pad Layout



| Symbol | Unit (mm) | Unit (inch) |
|--------|-----------|-------------|
| A      | 1.2       | 0.047       |
| B      | 1.2       | 0.047       |
| C      | 3.2       | 0.126       |
| D      | 2         | 0.079       |
| E      | 4.4       | 0.173       |