


FEATURES

- $R_{DS(ON)} \leq 17m\Omega @ V_{GS}=10V$ (N-Ch)
- $R_{DS(ON)} \leq 58m\Omega @ V_{GS}=4.5V$ (N-Ch)
- $R_{DS(ON)} \leq 32m\Omega @ V_{GS}=-10V$ (P-Ch)
- $R_{DS(ON)} \leq 75m\Omega @ V_{GS}=-4.5V$ (P-Ch)

Application

- Motor/Body Load Control
- Load Switch
- PWM Application
- DC-DC converters and Off-line UPS

PIN CONFIGURATION



Marking: 4012

Absolute Maximum Ratings (at $T_a = 25^\circ C$ unless otherwise specified)

Parameter	Symbol	N-Channel	P-Channel	Unit
Drain-Source Voltage	V_{DSS}	40	-40	V
Gate-Source Voltage	V_{GSS}	± 25	± 25	V
Continuous Drain Current($T_j=150^\circ C$)*	$T_c=25^\circ C$	I_D	22.1	A
	$T_c=70^\circ C$		17.7	
	$T_A=25^\circ C$		7.4	
	$T_A=70^\circ C$		5.9	
Pulsed Drain Current	I_{DM}	30	-30	A
Maximum Power Dissipation	$T_A=25^\circ C$	P_D	2.6	W
	$T_A=70^\circ C$		1.67	
Operating Junction Temperature	T_J	-55 to 150		
Thermal Resistance-Junction to Ambient*	$R_{\theta JA}$	Steady	48	$^\circ C/W$
		10sec	20	
Thermal Resistance-Junction to Case*	$R_{\theta JC}$	5.3		5 $^\circ C/W$














Electrical Characteristics (at $T_a = 25^\circ\text{C}$ unless otherwise specified)







Symbol	Parameter	Limit		Min	Typ	Max	Unit
STATIC							
$V_{(\text{BR})\text{DSS}}$	Drain-Source Breakdown Voltage	$V_{GS}=0\text{V}, I_D=250\ \mu\text{A}$ $V_{GS}=0\text{V}, I_D=-250\ \mu\text{A}$	N-Ch P-Ch	40 -40			V
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=250\ \mu\text{A}$ $V_{DS}=V_{GS}, I_D=-250\ \mu\text{A}$	N-Ch P-Ch	1 -1	1.5 -1.5	3 -3	V
I_{GSS}	Gate Leakage Current	$V_{DS}=0\text{V}, V_{GS}=\pm 25\text{V}$ $V_{DS}=0\text{V}, V_{GS}=\pm 25\text{V}$	N-Ch P-Ch			± 100 ± 100	nA
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=40\text{V}, V_{GS}=0\text{V}$ $V_{DS}=-40\text{V}, V_{GS}=0\text{V}$	N-Ch P-Ch			1 -1	μA
		$V_{DS}=40\text{V}, V_{GS}=0\text{V}, T_J=55^\circ\text{C}$ $V_{DS}=-40\text{V}, V_{GS}=0\text{V}, T_J=55^\circ\text{C}$	N-Ch P-Ch			10 -10	
$R_{DS(\text{ON})}$	Drain-Source On-State Resistance ^a	$V_{GS}=10\text{V}, I_D=7\text{A}$ $V_{GS}=-10\text{V}, I_D=-7\text{A}$	N-Ch P-Ch		17 32	30 45	$\text{m}\Omega$
		$V_{GS}=4.5\text{V}, I_D=6\text{A}$ $V_{GS}=-4.5\text{V}, I_D=-6\text{A}$	N-Ch P-Ch		42 58	58 75	
V_{SD}	Diode Forward Voltage	$I_S=1.7\text{A}, V_{GS}=0\text{V}$ $I_S=-1.7\text{A}, V_{GS}=0\text{V}$	N-Ch P-Ch		0.7 -0.7	1.2 -1.2	V
DYNAMIC							
Q_g	Total Gate Charge	N-Channel $V_{DS}=20\text{V}, V_{GS}=4.5\text{V}, I_D=7\text{A}$ P-Channel $V_{DS}=-20\text{V}, V_{GS}=-4.5\text{V}, I_D=-7\text{A}$	N-Ch P-Ch		8 10		nC
Q_{gs}	Gate-Source Charge		N-Ch P-Ch		4 4.3		
Q_{gd}	Gate-Drain Charge		N-Ch P-Ch		4 4.5		
R_g	Gate Resistance	$V_{GS}=0\text{V}, V_{DS}=0\text{V}, f=1\text{MHz}$ $V_{GS}=0\text{V}, V_{DS}=0\text{V}, f=1\text{MHz}$	N-Ch P-Ch		0.7 6		Ω
C_{iss}	Input capacitance	N-Channel $V_{DS}=20\text{V}, V_{GS}=0\text{V}, F=1\text{MHz}$ P-Channel $V_{DS}=-20\text{V}, V_{GS}=0\text{V}, F=1\text{MHz}$	N-Ch P-Ch		560 860		pF
C_{oss}	Output Capacitance		N-Ch P-Ch		72 120		
C_{rss}	Reverse Transfer Capacitance		N-Ch P-Ch		18 35		
$t_{d(on)}$	Turn-On Delay Time	N-Channel $V_{DD}=15\text{V}, R_L=15\Omega$ $I_D=1\text{A}, V_{GEN}=10\text{V}, R_G=6\Omega$ P-Channel $V_{DD}=-15\text{V}, R_L=15\Omega$ $I_D=-1\text{A}, V_{GEN}=-10\text{V}, R_G=6\Omega$	N-Ch P-Ch		11 30		ns
t_r	Turn-On Rise Time		N-Ch P-Ch		13 8.5		
$t_{d(off)}$	Turn-Off Delay Time		N-Ch P-Ch		37 70		
t_f	Turn-On Fall Time		N-Ch P-Ch		3.5 7		






Notes: a. Pulse test; pulse width $\leq 300\text{us}$, duty cycle $\leq 2\%$




Typical Characteristics









Package Outline Dimensions TO-252-4L Package

DIM	MILLIMETERS (mm)	
	MIN	MAX
A	2.20	2.50
A1	1.10	1.30
B	0.30	0.75
B1	0.55	0.75
B2	0.40	0.80
C	0.40	0.60
D	5.20	5.70
D2	6.50	7.30
D3	2.20	3.00
E	6.30	6.70
E2	4.50	5.50
H	9.50	10.50
L	1.30	1.70
L1	0.90	1.70
L2	0.50	1.10
L3	0.00	0.30
P	1.20	1.40