

Compensated High Current Choke, 3-phase



See below:

Approvals and Compliances

Description

- Current compensated choke
- 3-phase choke
- Flexible wire
- Flange for mounting onto printed circuit board
- Fully potted resign

Applications

- Placed in front of frequency converter
- Stepper motor drives
- UPS-systems
- Inverter

References

Weblinks

[pdf data sheet](#), [html datasheet](#), [General Product Information](#), [Approvals](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated voltage	up to 540VAC	Test Voltage	2.5kV, 50Hz, 2 sec. winding to winding	
	up to 760VDC		Isolation Voltage	2.5kV eff., 50Hz, 2 sec, winding to ambient
	UL 600 VAC			Climatic Category
Rated Current	10 - 50A @ Ta 40 °C	Allowable Operation Temp.	-25 °C to 100 °C	
Rated inductance	0.6 - 5mH, Tol. -30% +50%			
Power Operating Frequency	50 / 60Hz			
Terminal Type	Flexible wire			
Weight	145 - 1864 g			
Material	UL 94V-0			
Sealing Compound	UL 94V-0			

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in [Details about Approvals](#)

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Approvals

The approval mark is used by the testing authorities to certify compliance with the safety requirements placed on electronic products.

Approval Reference Type: DKIP

Approval Logo	Certificates	Certification Body	Description
	UL Approvals	UL	UR File Number: E72928






Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
	Suitable for applications acc.	IEC/UL 62368-1	Audio/video, information and communication technology equipment - Part 1: Safety requirements


Compliances

The product complies with following Guide Lines


Identification	Details	Initiator	Description
	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
	UKCA declaration of conformity	SCHURTER AG	The UKCA marking declares that the product complies with the applicable requirements laid down in the British Amendment of Regulation (EC) 765/2008.
	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimensions [mm]


Case 29-3W



Case 31-3W




Case 33-3W




Impedance curves


DKIP-0329-xxxx



DKIP-0331-xxxx



DKIP-0333-xxxx



All Variants

I_n [A]	L_n [mH]	R_{cu} [mΩ]	Tripped Power Dissipation [W]	f_{RES} [MHz]	Copper ϕ [mm]	Weight [g]	Housing	Packing unit [pcs.]	Order Number
10	2.5	15	4.5	0.5	1.25	145 g	29-3W	12	DKIP-0329-1002
15	1	7	4.7	0.6	1.6	145 g	29-3W	12	DKIP-0329-1501
20	0.6	5	6	2.6	1.8	145 g	29-3W	12	DKIP-0329-20D6
10	5	32	9.6	0.22	1.25	526 g	31-3W	2	DKIP-0331-1005
15	2	13	8.8	0.44	1.6	544 g	31-3W	2	DKIP-0331-1502
20	1	8	9.6	0.68	1.8	544 g	31-3W	2	DKIP-0331-2001
25	4	12	22.5	0.18	2	1830 g	33-3W	1	DKIP-0333-2504
36	2	7.6	29.5	0.25	2.36	1831 g	33-3W	1	DKIP-0333-3602
50	1	4	30	0.5	1.5 x 4.5	1864 g	33-3W	1	DKIP-0333-5001

Availability for all products can be searched real-time: <https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>