

Features

- ◆ Low operating voltage: 24V
- ◆ Ultra low leakage: nA level
- ◆ Complies with following standards:
 - ◆ – IEC 61000-4-2 (ESD) immunity test
 - Air discharge: 30kV
 - Contact discharge: ± 30 kV
 - ◆ – IEC61000-4-5 (Lightning)7A (8/20 μ s)
- ◆ RoHS Compliant
- ◆ Lead Finish: NiPdAu


Mechanical Characteristics

- ◆ Package: SOT23-6
- ◆ Lead Finish: Matte Tin
- ◆ Case Material: "Green" Molding Compound.
- ◆ UL Flammability Classification Rating 94V-0
- ◆ Moisture Sensitivity: Level 3 per J-STD-020
- ◆ Shipping Qty :3000 /7Inch Tape & Reel

Applications

- ◆ Networking and Telecom
- ◆ Automotive Electronics
- ◆ Serial and Parallel Ports
- ◆ Notebooks, Desktops, Servers

Dimensions and Pin Configuration



Marking: 6M8

Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	300	W
Peak Pulse Current (8/20μs)	Ipp	7	A
ESD per IEC 61000-4-2 (Air)	VESD	±30	kV
ESD per IEC 61000-4-2 (Contact)		±30	
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM			24	V	Any I/O pin to ground
Punch-Through Voltage	VBR	26.7			V	IT = 1mA, any I/O pin to ground
Reverse Leakage Current	IR			1	μA	VRWM = 24V, any I/O pin to ground
Clamping Voltage	VC		45		V	I _{PP} = 7A (8 x 20us pulse), any I/O pin to ground
Junction Capacitance	CJ			100	pF	VR=0, f=1MHz, between I/O pins

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)







Fig3. Power Derating Curve




Outline Drawing - SOT23-6



DIM	INCHES			MILLIMETERS		
	MIN	NOM	MAX	MIN	NOM	MAX
A	.035	-	.057	0.90	-	1.45
A1	.000	-	.006	0.00	-	0.15
A2	.035	.045	.051	.90	1.15	1.30
b	.010	-	.020	0.25	-	0.50
c	.003	-	.009	0.08	-	0.22
D	.110	.114	.118	2.80	2.90	3.00
E1	.060	.063	.069	1.50	1.60	1.75
E	.110 BSC			2.80 BSC		
e	.037 BSC			0.95 BSC		
e1	.075 BSC			1.90 BSC		
L	.012	.018	.024	0.30	0.45	0.60
L1	(.024)			(0.60)		
N	6			6		
θ1	0°	-	10°	0°	-	10°
aaa	.004			0.10		
bbb	.008			0.20		
ccc	.008			0.20		

Land Pattern - SOT23-6



DIM	DIMENSIONS	
	INCHES	MILLIMETERS
C	(.098)	(2.50)
G	.055	1.40
P	.037	0.95
X	.024	0.60
Y	.043	1.10
Z	.141	3.60