

◆ Features:





- ◊ Fast switching speed
开关速度快
- ◊ Low gate charge
低门充電
- ◊ High power and current handing capability
高功率和电流处理能力
- ◊ RoHS compliant
符合 RoHS 标准

**TO-252**

1

◆ Applications

- ◊ DC to DC converters
直流到直流转换
- ◊ Synchronous Rectification
同步整流



单位: mm
TO-252



OSD90N02T

LOW Voltage Nch MOSFET

<http://www.osen.net.cn>

◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings		Unit
V _{DSS}	Drain-Source Voltage 漏源电压	20		V
V _{GS}	Gate-Source Voltage-Continuous 栅源电压	±10		V
I _D	Drain Current-Continuous (Note 2) 漏极持续电流	90		A
I _{DM}	Drain Current-Single Plused (Note 1) 漏极单次脉冲电流	360		A
P _D	Power Dissipation (Note 2) 功率损耗	85		W
T _j	Max.Operating junction temperature 最大结温	150		°C

◆ Electrical characteristics (Tc=25°C unless otherwise noted)

Symbol	Parameters	Min	Typ	Max	Units	Conditions
Static Characteristics						
B _{VDSS}	Drain-Source Breakdown VoltageCurrent (Note 1) 漏极击穿电压	20	--	--	V	I _D =250μA, V _{GS} =0V
V _{GS(th)}	Gate Threshold Voltage 栅极开启电压	0.4	0.7	1.0	V	V _{DS} =V _{GS} , I _D =250μA
R _{DS(on)}	Drain-Source On-Resistance 漏源导通电阻	--	3.1	5	mΩ	V _{GS} =4.5V, I _D =20A
I _{GSS}	Gate-Body Leakage Current 栅极漏电流	--	--	±100	nA	V _{GS} =±10V, V _{DS} =0
I _{DSS}	Zero Gate Voltage Drain Current 零栅极电压漏极电流	--	--	1	μA	V _{DS} =20V, V _{GS} =0
g _{fS}	Forward Transconductance 正向跨导	--	12	--	S	V _{DS} =5V, I _D =10A



OSD90N02T

LOW Voltage Nch MOSFET

Switching Characteristics

$T_{d(on)}$	Turn-On Delay Time 开启延迟时间	--	10	--	ns	$V_{GS}=4.5V$, $V_{DS}=10V, I_D=50A$, $R_G=2.5\Omega$
T_r	Rise Time 上升时间	--	40	--	ns	
$T_{d(off)}$	Turn-Off Delay Time 关闭延迟时间	--	65	--	ns	
T_f	Fall Time 下降时间	--	50	--	ns	
Q_g	Total Gate Charge 栅极总电荷	--	35	--	nC	$V_{DS}=10V$, $V_{GS}=4.5V$, $I_D=50A$
Q_{gs}	Gate-Source Charge 栅源极电荷	--	4.0	--	nC	
Q_{gd}	Gate-Drain Charge 栅漏极电荷	--	15	--	nC	

Dynamic Characteristics

C_{iss}	Input Capacitance 输入电容	--	2450	--	pF	$V_{DS}=10V, V_{GS}=0$, $f=1MHz$
C_{oss}	Output Capacitance 输出电容	--	450	--	pF	
C_{rss}	Reverse Transfer Capacitance 反向传输电容	--	455	--	pF	
I_S	Continuous Drain-Source Diode Forward Current (Note 2) 二极管导通正向持续电流	--	--	40	A	
V_{SD}	Diode Forward On-Voltage 二极管正向导通电压	--	--	1.3	V	$I_S=40A, V_{GS}=0$
$R_{th(j-c)}$	Thermal Resistance, Junction to Case 结到外壳的热阻	--	--	1.47	°C/W	

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW <= 300us , duty cycle <= 2%.