

◆ **Features:**




- ◇ Fast switching speed
开关速度快
- ◇ Low gate charge
低门充电
- ◇ High power and current handling capability
高功率和电流处理能力
- ◇ RoHS compliant
符合 RoHS 标准

◆ **Applications**

- ◇ DC to DC converters
直流到直流转换
- ◇ Synchronous Rectification
同步整流



TO-220





OSP150N08G

N-Channel Power Trench MOSFET®

◆ Absolute Maximum Ratings (Tc=25°C)

| Symbol | Parameters | Ratings | Unit |
|------------------|--------------------------------------------------|---------|------|
| V _{DSS} | Drain-Source Voltage 漏源电压 | 80 | V |
| V _{GS} | Gate-Source Voltage-Continuous 栅源电压 | ±20 | V |
| I _D | Drain Current-Continuous (Note 2) 漏极持续电流 | 150 | A |
| I _{DM} | Drain Current-Single Plused (Note 1) 漏极单次脉冲电流 | 600 | A |
| P _D | Power Dissipation (Note 2) 功率损耗 | 300 | W |
| T _j | Max.Operating junction temperature 最大结温 | 150 | °C |

◆ Electrical characteristics (Tc=25°C unless otherwise noted)

| Symbol | Parameters | Min | Typ | Max | Units | Conditions |
|-------------------------------|---------------------------------------------------|-----|-----|------|-------|----------------------------------------------------------|
| Static Characteristics | | | | | | |
| B _{VDS} | Drain-Source Breakdown Voltage 漏极击穿电压 (Note 1) | 80 | -- | -- | V | I _D =250μA, V _{GS} =0V |
| V _{GS(th)} | Gate Threshold Voltage 栅极开启电压 | 2.0 | -- | 4.0 | V | V _{DS} =V _{GS} , I _D =250μA |
| R _{DS(on)} | Drain-Source On-Resistance 漏源导通电阻 | -- | 3.5 | 4.0 | mΩ | V _{GS} =10V, I _D =20A |
| I _{GSS} | Gate-Body Leakage Current 栅极漏电流 | -- | -- | ±100 | nA | V _{GS} =±20V, V _{DS} =0 |
| I _{DSS} | Zero Gate Voltage Drain Current 零栅极电压漏极电流 | -- | -- | 1 | μA | V _{DS} =100V, V _{GS} =0 |
| g _{fs} | Forward Transconductance 正向跨导 | -- | 55 | -- | S | V _{DS} =10V, I _D =50A |

| Switching Characteristics | | | | | | |
|---------------------------|--------------------------------------------------------------------------|----|-------------|-------------|---------------|---------------------------------------------|
| $T_{d(on)}$ | Turn-On Delay Time 开启延迟时间 | -- | 15 | -- | ns | $V_{DD}=40V, I_D=20A,$ $R_G=5\Omega$ |
| T_r | Rise Time 上升时间 | -- | 55 | -- | ns | |
| $T_{d(off)}$ | Turn-Off Delay Time 关闭延迟时间 | -- | 65 | -- | ns | |
| T_f | Fall Time 下降时间 | -- | 50 | -- | ns | |
| Q_g | Total Gate Charge 栅极总电荷 | -- | 140 | -- | nC | $V_{DS}=40V,$ $V_{GS}=10V,$ $I_D=50A$ |
| Q_{gs} | Gate-Source Charge 栅源极电荷 | -- | 35 | -- | nC | |
| Q_{gd} | Gate-Drain Charge 栅漏极电荷 | -- | 45 | -- | nC | |
| Dynamic Characteristics | | | | | | |
| C_{iss} | Input Capacitance 输入电容 | -- | 5550 | -- | pF | $V_{DS}=25V, V_{GS}=0,$ $f=1MHz$ |
| C_{oss} | Output Capacitance 输出电容 | -- | 1900 | -- | pF | |
| C_{rss} | Reverse Transfer Capacitance 反向传输电容 | -- | 325 | -- | pF | |
| I_S | Continuous Drain-Source Diode Forward Current (Note 2) 二极管导通正向持续电流 | -- | -- | 150 | A | |
| V_{SD} | Diode Forward On-Voltage 二极管正向导通电压 | -- | -- | 1.3 | V | $I_S=60A, V_{GS}=0$ |
| $R_{th(j-c)}$ | Thermal Resistance, Junction to Case 结到外壳的热阻 | -- | -- | 0.58 | $^{\circ}C/W$ | |

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW \leq 300us , duty cycle \leq 2%.