




**◆ Features:**

- ◆ Very Low FOM  $R_{DS(on)}$   
低内阻
- ◆ %100 avalanche tested  
%100 雪崩能量测试
- ◆ RoHS compliant  
RoHS 认证
- ◆ Improved dv/dt capability, high ruggedness  
提高 dv/dt 能力, 高耐用性

**◆ Applications**

- ◆ High efficiency switch mode power supplies  
高效率开关电源
- ◆ Power factor correction  
功率因数校正
- ◆ Electronic lamp ballast  
电子整流器



单位: mm  
**TO-220F**



OSPF65R280

650V super-junction Power MOSFET

<http://www.osen.net.cn>

## ◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings		Unit
V <sub>DSS</sub>	Drain-Source Voltage 漏源电压	<b>650</b>		V
V <sub>GS</sub>	Gate-Source Voltage-Continuous 栅源电压	<b>±30</b>		V
I <sub>D</sub>	Drain Current-Continuous (Note 2) 漏极持续电流	<b>15</b>		A
I <sub>DM</sub>	Drain Current-Single Plused (Note 1) 漏极单次脉冲电流	<b>45</b>		A
P <sub>D</sub>	Power Dissipation (Note 2) 功率损耗	<b>40</b>		W
T <sub>j</sub>	Max.Operating junction temperature 最大结温	<b>150</b>		°C

Symbol	Parameters	Min	Typ	Max	Units	Conditions
<b>Static Characteristics</b>						
B <sub>VDS</sub>	Drain-Source Breakdown VoltageCurrent (Note 1) 漏极击穿电压	<b>650</b>	--	--	V	I <sub>D</sub> =250μA, V <sub>GS</sub> =0V, T <sub>j</sub> =25°C
V <sub>GS(th)</sub>	Gate Threshold Voltage 栅极开启电压	<b>2.0</b>	--	<b>4.0</b>	V	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA
R <sub>DS(on)</sub>	Drain-Source On-Resistance 漏源导通电阻	--	<b>0.22</b>	<b>0.28</b>	Ω	V <sub>GS</sub> =10V, I <sub>D</sub> =7.5A
I <sub>GSS</sub>	Gate-Body Leakage Current 栅极漏电流	--	--	<b>±100</b>	nA	V <sub>GS</sub> =±30V, V <sub>DS</sub> =0
I <sub>DSS</sub>	Zero Gate Voltage Drain Current 零栅极电压漏极电流	--	--	<b>1</b>	μA	V <sub>DS</sub> =600V, V <sub>GS</sub> =0
<b>Switching Characteristics</b>						



OSPF65R280

<http://www.osen.net.cn>

650V super-junction Power MOSFET

$T_{d(on)}$	Turn-On Delay Time 开启延迟时间	--	<b>35</b>	--	ns	$V_{DS}=350V, I_D=15A$ $R_G=25\Omega$
$T_r$	Rise Time 上升时间	--	<b>15</b>	--	ns	
$T_{d(off)}$	Turn-Off Delay Time 关闭延迟时间	--	<b>105</b>	--	ns	
$T_f$	Fall Time 下降时间	--	<b>5</b>	--	ns	
$Q_g$	Total Gate Charge 栅极总电荷	--	<b>25</b>	--	nC	$V_{DS}=480V, V_{GS}=15V$ $I_D=11A$
$Q_{gs}$	Gate-Source Charge 栅源极电荷	--	<b>8</b>	--	nC	
$Q_{gd}$	Gate-Drain Charge 栅漏极电荷	--	<b>10</b>	--	nC	
<b>Dynamic Characteristics</b>						

$C_{iss}$	Input Capacitance 输入电容	--	<b>1100</b>	--	pF	$V_{DS}=50V, V_{GS}=0$ $f=1MHz$
$C_{oss}$	Output Capacitance 输出电容	--	<b>75</b>	--	pF	
$C_{rss}$	Reverse Transfer Capacitance 反向传输电容	--	<b>6.5</b>	--	pF	
$I_S$	Continuous Drain-Source Diode Forward Current 二极管导通正向持续电流	--	--	<b>15</b>	A	
$V_{SD}$	Diode Forward On-Voltage 二极管正向导通电压	--	--	<b>1.3</b>	V	$I_S=15A, V_{GS}=0$
$R_{th(j-c)}$	Thermal Resistance, Junction to Case 结到外壳的热阻	--	--	<b>3.13</b>	°C/W	

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW &lt;= 300us , duty cycle &lt;= 2%.