


30BQ040

Technical Data Data Sheet N0674, Rev. A



30BQ040 SCHOTTKY RECTIFIER



Circuit Diagram



Features

- Small foot print, surface moutable
- Low forward voltage drop
- High frequency operation
- Guard ring for enhanced ruggedness and long term reliability
- Terminals finish: 100% Pure Tin
- This is a Pb Free Device
- All SMC parts are traceable to the wafer lot
- Additional testing can be offered upon request

Applications

- Disk Drives
- Switching power supply
- Redundant power subsystems
- Converters
- Free-Wheeling diodes
- Reverse battery protection
- Battery Charging

Maximum Ratings:

Characteristics	Symbol	Condition	Max.	Units
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM} V _{RWM} V _R	-	40	V
Average Rectified Forward Current	IF (AV)	50% duty cycle @T _c =118°C, rectangular wave form	3.0	А
Peak One Cycle Non-Repetitive Surge Current	I _{FSM}	8.3 ms, half Sine pulse, T_c =25°C	80	А

Electrical Characteristics:

Characteristics	Symbol	Condition	Тур.	Max.	Units
Forward Voltage Drop*	V _{F1}	@ 3 A, Pulse, T _J = 25 °C	0.50	0.53	V
		@ 6 A, Pulse, T _J = 25 °C	0.65	0.68	v
	V _{F2}	@ 3 A, Pulse, T _J = 125 °C	0.40	0.43	V
		@ 6 A, Pulse, TJ = 125°C	0.55	0.57	v
Reverse Current*	I _{R1}	@V _R = Rated V _R , Pulse, T _J = 25 °C	0.01	0.5	mA
	I _{R2}	@V _R = Rated V _R , Pulse, T _J = 100 °C	7	30	mA
Junction Capacitance	Ст	@V _R = 5V, T _C = 25 °C f _{SIG} = 1MHz	130	230	pF
Series Inductance	Ls	Measured lead to lead 5 mm from 3 gackage body		-	nH
Voltage Rate of Change	dv/dt	-	-	10,000	V/µs

^{*} Pulse width < 300 μ s, duty cycle < 2%

• China - Germany - Korea - Singapore - United States •

http://www.smc-diodes.com - sales@ smc-diodes.com •




Technical Data Data Sheet N0674, Rev. A

Thermal-Mechanical Specifications:

Characteristics	Symbol	Condition	Specification	Units
Junction Temperature	TJ	-	-55 to +125	°C
Storage Temperature	T _{stg}	-	-55 to +150	°C
Typical Thermal Resistance Junction to Lead	R _{0JL}	-	12	°C/W
Typical Thermal Resistance Junction to Case	$R_{ heta JA}$	DC operation	46	°C/W
Approximate Weight	wt	-	0.21	g
Case Style	SMC			

Ratings and Characteristics Curves



Typical Forward Characteristics

China - Germany - Korea - Singapore - United States http://www.smc-diodes.com - sales@ smc-diodes.com -

30BQ040


RoHS 🗭

Typical Reverse Characteristics



Technical Data Data Sheet N0674, Rev. A

Mechanical Dimensions SMC




Ordering Information

Device	Package	Shipping
30BQ040	SMC (Pb-Free)	3000pcs / reel
30BQ040TR	SMC (Pb-Free)	3000pcs / reel

For information on tape and reel specifications, including part orientation and tape sizes, please refer to our tape and reel packaging specification.

Carrier Tape Specification SMC



SYMBOL	Millin	limeters		
STWIDOL	Min.	Max.		
A	5.90	6.10		
В	8.20	8.40		
C	2.40	2.60		
d	1.40	1.60		
E	1.40	1.60		
F	7.60	7.70		
Р	7.90	8.10		
P0	3.90	4.10		
P1	3.90	4.10		
Т	-	0.600		
W	15.80	16.20		

• China - Germany - Korea - Singapore - United States • • http://www.smc-diodes.com - sales@ smc-diodes.com •

Г

- 11	SYMBOL						
	STNIBOL	Min.	Max.	Min.	Max.		
	А	5.59	6.22	0.220	0.245		
	В	6.60	7.11	0.260	0.280		
	С	2.75	3.25	0.108	0.128		
	D	0.152	0.305	0.006	0.012		
	Е	7.75	8.25	0.305	0.325		
	F	2.00	2.95	0.079	0.116		
	G	0.051	0.203	0.002	0.008		
	Н	0.76	1.60	0.030	0.063		

Millimeters

Marking Diagram

Where XXXXX is YYWWL



SC3F = Part Name = Year = Week = Lot Number

YY

Т

WW

Cautions: Molding resin Epoxv resin UL:94V-0

30BQ040



Inches



Technical Data Data Sheet N0674, Rev. A





DISCLAIMER:

1- The information given herein, including the specifications and dimensions, is subject to change without prior notice to improve product characteristics. Before ordering, purchasers are advised to contact the SMC Diode Solutions sales department for the latest version of the datasheet(s).

2- In cases where extremely high reliability is required (such as use in nuclear power control, aerospace and aviation, traffic equipment, medical equipment, and safety equipment), safety should be ensured by using semiconductor devices that feature assured safety or by means of users' fail-safe precautions or other arrangement.

3- In no event shall SMC Diode Solutions be liable for any damages that may result from an accident or any other cause during operation of the user's units according to the datasheet(s). SMC Diode Solution assumes no responsibility for any intellectual property claims or any other problems that may result from applications of information, products or circuits described in the datasheets.

4- In no event shall SMC Diode Solutions be liable for any failure in a semiconductor device or any secondary damage resulting from use at a value exceeding the absolute maximum rating.

5- No license is granted by the datasheet(s) under any patents or other rights of any third party or SMC Diode Solutions.

6- The datasheet(s) may not be reproduced or duplicated, in any form, in whole or part, without the expressed written permission of SMC Diode Solutions.

7- The products (technologies) described in the datasheet(s) are not to be provided to any party whose purpose in their application will hinder maintenance of international peace and safety nor are they to be applied to that purpose by their direct purchasers or any third party. When exporting these products (technologies), the necessary procedures are to be taken in accordance with related laws and regulations..

• China - Germany - Korea - Singapore - United States •

http://www.smc-diodes.com - sales@ smc-diodes.com -