
AT ALL TIMES WATER RESISTANT (5:1)Ø1,12 (9x) CONNECTORS NOT IN USE SHOULD BE COVERED WITH A CONEC WATER RESISTANT CAP OR WATER TIGHT HOOD. **SEALING COMPOUND** 10,66 +0,4 $30,88^{+0,3}_{-0,15}$ $25^{+0,12}_{-0,13}$ 2,55 +0,25 +0,12 -0,18 $16,81^{+0,23}_{-0,02}$ POS. 1-**SEALING** 5,64 POS. 6 **GASKET** $12.8^{+0.3}_{-0.15}$ $8,23^{+0,25}_{-0}$ ******* 0 0 **RUBBER GASKET PLACED** ON TOP SURFACE OF MALE 10° **INSULATOR** 4-40 UNC SEE NOTE 13 SW4,8 4-40 UNC (d) NOTES: 1. RECOMMENDED SOLDER INSTRUCTION SEE SHEET 2 2. IP RATING: IP 67 3. SEALED TO WITHSTAND PRESSURE UP TO 1,45 PSI FOR 30 MINUTES AFTER SOLDERING 4. METALSHELL: ZINC DIE CAST; min. 50µin NICKEL PLATING over COPPER 5. INSULATORS: PBT GF UL 94 V-0 6. SEALING GASKET: SILICONE 7. RUBBER GASKET: TPE 8. SEALING COMPOUND: EPOXY RESIN UL 94 V-0 9. CONTACTS: COPPER ALLOY; PLATING (SEE PART-NO.): □ PLEASE ADD 1 for 30μin HARD GOLD over min. 50μin NICKEL ☐ PLEASE ADD 3 for GOLD FLASH over NICKEL SOLDER CUP ACCEPTS CABLE AWG 20 10. HEXLOCKING SCREWS: STAINLESS STEEL 11. RECOMMENDED PANEL CUT-OUT ON SHEET 2 12. RECOMMENDED TORQUE FOR MOUNTING SCREW 35Ncm (3.1 in.LB) / max.67Ncm (6 in.LB) 13. CONNECTOR IS PART MARKED: 15-00624 CONEC ABC (see note 9) scale: 2:1 (5:1) THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN AMY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPPRIGHT OF CONEC GMBH DRAWING BY HAND tolerance material: SEE NOTES dim. in mm date name title: **D-SUB MALE** 10.09.14 9pos. SOLDER CUP appd. 26.01.15 Fischer CAD Ä6417 06.03.17 Lehm. with closed 4-40 UNC thread dwg no: ALTER (DIN-1 x c Ä5827 24.09.15 Unkrüer d-old 2 x b 15.09.15 АЗ Ä5817 M.H. 15K1A1533 NOT Original sh: 1 RoHS compliant rev. description part no: 15-00624□ date (see note 9)

Solder Instruction

- 1. Cable should be prepared for soldering. The cable/wires must be pretinned.
- 2. Insert cable/wire into solder cup.
- 3. Operate the soldering iron at 350°C, 50 Watt max. and use a pencil tip.
- 4. Apply some solder to the solder tip of the soldering iron.
- 5. Put tip to wire in solder cup.
- 6. After 1 second bring in solder.
- 7. Heat for 3 seconds longer. Do not heat contact more than 4 seconds in total.
- 8. Remove soldering iron.
- 9. Wait until solder gets rigid again.
- 10. Do not solder adjacent contacts consecutively, alternate position within the connector to minimize heat build up.

RECOMMENDED PANEL CUT-OUT



	AY NOT BE COPIED OR ANY WAY, AND MAY NOT) A THIRD PARTY WITHOUT SION. COPYRIGHT OF CONEC GMbH	DRAWING BY HAND					tolerance			scale: 5:1 material: SEE SHEET 1
TOTAL YANG									dim. in mm	SEE SHEET I
								date	name	title:
							drawn	10.09.14	Lehmenkühler	RECOMMENDED PANEL CUT-OUT
							appd.	26.01.15	Fischer	D-SUB MALE 9pos. SOLDER CUP
		ALTER CAD					norm			with closed 4-40 UNC thread
	NI DI NI						d-old			dwg no: DIN-
			1 x c	Ä5827	24.09.15	Unkrüer		45 E		15K1A1533
	DRA ODU ASSE TEN ERSF	NOT	а	Original					ΝΕ₹°	sh: 2
	THIS DRAWI REPRODUCE BE PASSED (WRITTEN PE OWNERSHIP	D0 I	rev.	description	date	date name			11.6	part no: SEE SHEET 1