

# **Engineering/Process Change Notice**

ECN/PCN No.: 4111

For Manufacturer							
Product Description: PLASTIC SMD MEMS OSCILLATOR	Abracon Part Numb	oer / Part Series: MK06	<ul><li>□ Documentation only</li><li>□ ECN</li><li>⋈ EOL</li></ul>	Series     □ Part Number			
Affected Revision:	New Revision:	OL	Application:	☐ Safety ☑ Non-Safety			
Prior to Change: Active https://abracon.com/Oscillators/ASTMK06	5.pdf			·			
After Change: EOL							
Cause/Reason for Change: Discontinuation of manufacturing capability	ty.						
	Chan	ge Plan					
Effective Date: 2/7/2022	Additional Remarks	:					
Change Declaration: N/A							
Issued Date: 2/7/2022	Issued By:  Brooke Cushman		Issued Department: Engineering				
		Engineer					
Approval:  Thomas Culhane  Engineering Director	Approval:  Reuben Quintanilla  Quality Director		Approval:  Ying Huang  Purchasing Director				
For Abracon EOL only							
Last Time Buy (if applicable):  5/7/2022  Alternate Part Number / Part Series: none							
Additional Approval:	Additional Approval	:	Additional Approval:				
	Customer Appro	oval (If Applicable)					
<b>Qualification Status:</b> Note: It is considered approved if there is n		☐ Not accepted ustomer 1 month after	r ECN/PCN is released.				
Customer Part Number:		Customer Project:					
Company Name:	Company Represent	ative:	Representative Signature	:			
Customer Remarks:							



Form #7020 | Rev. G | Effective: 02/22/2021 |











ASTMK06







Moisture Sensitivity Level (MSL) – 1

### **FEATURES:**

- Ultra-miniature size: 2.0 x 1.2 x 0.6mm
- Supply Voltage: 1.5V to 3.63V
- Ultra-Low Current Consumption: 1.0µA typ.(no load)
- Frequency Stabilities include:
  - $\pm 75$ ppm over -10 to  $\pm 70$ °C
  - $\pm 100$ ppm over -40 to +85°C
- Internal power supply filtering eliminates external bypass capacitor for Vdd port.



### > APPLICATIONS:

- General Timekeeping
- Battery Management
- Portable devices
- RTC reference clock
- Bluetooth/WiFi modules

### STANDARD SPECIFICATIONS:

Parameters	Min	Тур	Max	Unit	Notes
Output Frequency (F <sub>out</sub> )		32.768		kHz	
Initial Frequency Tolerance (F <sub>init</sub> ) (1)	-20		+20	ppm	$T_A$ = +25°C, post reflow, $V_{dd}$ :1.5-3.63V
Frequency Stability over Temperature $(F_{\text{stab}})^{(2)}$	-75 -100		+75 +100	ppm	$T_A$ = -10°C to +70°C, $V_{dd}$ :1.5-3.63V $T_A$ = -40°C to +85°C, $V_{dd}$ :1.5-3.63V
Aging (@+25°C)	-1		+1	ppm	First year
Supply Voltage (V <sub>dd</sub> )	1.5		3.63	V	T <sub>A</sub> = over temperature
		1.0			T <sub>A</sub> = +25°C, V <sub>dd</sub> :1.5-3.63V. No load.
Current Consumption ( I <sub>dd</sub>			1.9	μΑ	$T_A$ = -10°C to +70°C, $V_{dd}$ max: 3.63V. No load
			2.2		T <sub>A</sub> = -40°C to +85°C, V <sub>dd</sub> max: 3.63V. No load.
Power Supply Ramp (tydd_Ramp)			100	ms	Over temperature, 0 to 90% V <sub>dd</sub>
		180	300		$T_A$ = +25°C±10°C
Start-up Time at Power-up (T <sub>start</sub> )			450	ms	$T_A = -40^{\circ}C$ to $+70^{\circ}C$
			500		$T_A = +85$ °C
Operating Temperature Range (Tuse)	-10		+70	°C	Option "M"
	-40		+85		Option "L"
LVCMOS Output (T <sub>A</sub> = Over Temperatu	re. Typical val				
Output Rise/Fall Time (t <sub>r</sub> /t <sub>f</sub> )		100	200	ns	10-90%, 15pF load, V <sub>dd</sub> :1.5-3.63V
Output Clock Duty Cycle	48		52	%	
Output Voltage V <sub>OL</sub>	90%*V <sub>dd</sub>		10%*V <sub>dd</sub>	V	V <sub>dd</sub> :1.5-3.63V. I <sub>OH</sub> = -10μA, 15pF V <sub>dd</sub> :1.5-3.63V. I <sub>OL</sub> = 10μA, 15pF
Output Drive Level			50	pF	≥80% LVCMOS swing, V <sub>dd</sub> :1.8V, 2.5V, 3.3V
Period Jitter (T <sub>jitt</sub> )		35		ns <sub>RMS</sub>	Cycles – 10000, T <sub>A</sub> = +25°C

#### Note:

- Measured peak-to-peak. Tested with Agilent 53132A frequency counter. Due to the low operating frequency, the gate time must be ≥100ms to ensure an accurate frequency measurement.
- Measured peak-to-peak. Inclusive of initial tolerance at +25°C, and variations over operating temperature, rated power supply voltage and load.



ASTMK06






### **Absolute Maximum Ratings**


Attempted operation outside the absolute maximum ratings may cause permanent damage to the part. Actual performance of the IC is only guaranteed within the operational specifications, not at absolute maximum ratings.

Parameters	Test Condition	Value	Unit
Continuous Power Supply Voltage Range (V <sub>dd</sub> )		-0.5 to 3.63	V
Short Duration Max. Power Supply Voltage (V <sub>dd</sub> )	≤30 minutes	4.0	V
Short Duration Max. Operating Temperature Range	Vdd:1.5-3.63V, ≤30 minutes	125	°C
Human Body Model (HBM) ESD Protection	JESD22-A114	3000	V
Charge-Device Model (CDM) ESD Protection	JESD22-C101	750	V
Machine Model (MM) ESD Protection	JESD22-A115	300	V
Latch-up Tolerance	JESD78 Compli	iant	
Mechanical Shock Resistance	Mil 883, Method 2002	10000	g
Mechanical Vibration Resistance	Mil 883, Method 2007	70	g
2012 SMD Junction Temperature		150	$^{\circ}\mathbb{C}$
Storage Temperature		-65 to +150	°C

### **Block Diagram:**



### PART IDENTIFICATION:














### TYPICAL PERFORMANCE DATA (TA=25°C, Vdd=1.8V, unless otherwise stated)




### Supply Current vs Operating Temperature Range (No Load)




Power Supply Noise Rejection (±150mV Noise)




#### Frequency Stability vs. Operating Temperature Range



Start-up Time



LVCMOS Output Waveform ( $V_{\text{swing}} = 1.8V$ )






ASTMK06






### **OUTLINE DRAWING:**



### > REFLOW PROFILE:



Item	Conditions		
T <sub>S</sub> MAX to T <sub>L</sub> (Ramp-up Rate)	3°C/second max		
Preheat			
Temperature Minimum (T <sub>S</sub> MIN)	150°C		
Temperature Typical (T <sub>S</sub> TYP)	175°C		
Temperature Maximum (T <sub>S</sub> MAX)	200°C		
Time (t <sub>S</sub> )	60 – 180 seconds		
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )	3°C/second max		
Time Maintained Above			
Temperature (T <sub>L</sub> )	217℃		
Time (t <sub>L</sub> )	60 – 150 seconds		
Peak Temperature (T <sub>P</sub> )	260°C max		
Target Peak Temperature (T <sub>P</sub> Target)	255°C		
Time within 5°C of actual peak (t <sub>P</sub> )	20 – 40 seconds		
Max. Number of Reflow Cycles	3		
Ramp-down Rate	6°C/second max		
Time 25°C to Peak Temperature (t)	8 minutes max		




ASTMK06


Pb RoHS/RoHS II compliant



### **TAPE & REEL:**



<b>D</b> 0	D1 min.	<b>E</b> 1	E2 min.		P0	P1	P2
1.55±0.05	1.0	1.75±0.1	6.05	3.5±0.05	4.0±0.1	$4.0\pm0.1$	2.0±0.05
T	T1 max.	T2 max.	W max.	A0	В0	K0	
0.25±0.05	NA	NA	8.3	1.6±0.05	2.25±0.10	0.65±0.05	



	Option	A max.	B min.	C	D min.	N	W1	W2 max.
ſ	Т3	180.5	1.5	13.0+0.6/-0.2	20.2	60±0.5	8.4+1.5/-0	14.4
ſ	T10	330	1,5	13.0±0.2	20.2	100±0.5	8.4+1.5/-0	14.4

T3= Tape and reel (3,000pcs/reel) T10= Tape and reel (10,000pcs/reel)

Unit: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

