

ATGBICS AFBR-57R6APZ-NA1 Avago Broadcom Compatible Transceiver SFP+ 4.25/2.125/1.0625/1.25GBase-FC (850nm, MMF, 300m, DOM, Ext Temp)

Brand : ATGBICS

Product code: AFBR-57R6APZ-NA1-C

Product name : AFBR-57R6APZ-NA1 Avago Broadcom Compatible Transceiver SFP+ 4.25/2.125/1.0625/1.25GBase-FC (850nm, MMF, 300m, DOM, Ext Temp)



AFBR-57R6APZ-NA1 Avago Broadcom Compatible Transceiver SFP+ 4.25/2.125/1.0625/1.25GBase-FC (850nm, MMF, 300m, DOM, Ext Temp)

ATGBICS AFBR-57R6APZ-NA1 Avago Broadcom Compatible Transceiver SFP+ 4.25/2.125/1.0625/1.25GBase-FC (850nm, MMF, 300m, DOM, Ext Temp):



ATGBICS AFBR-57R6APZ-NA1 8.5/4.25/2.125GBase Fibre Channel transceiver supports a distance of up to 150m over multi-mode fibre (MMF) at 4.25gbps using a wavelength of 850nm via an LC connector. Digital optical monitoring (DOM) support is also present enabling real-time monitoring of the parameters of the fibre optic transceiver. Our product meets the specification of Avago AFBR-57R6APZ-NA1= and we proudly offer a compatibility guarantee and lifetime warranty. Our rigorously tested products record a unique traceable serial number and are fully compliant with all MSA Standards.

Performance		Features	
SFP transceiver type *	Fiber optic	Certification	CE, FCC, RoHS
Maximum data transfer rate *	4250 Mbit/s	Power	
Interface type *	SFP+	Input voltage	3.3 V
Single-mode fiber (SMF) supported	✗	Maximum voltage	3.5 V
Multi-mode fiber (MMF) supported	✓	Power consumption (typical)	1 W
Fiber optic connector	LC	Operational conditions	
SFP transceiver standard	SR	Minimum operating temperature	-10 °C
Maximum transfer distance	300 m	Maximum operating temperature	85 °C
Wavelength	850 nm	Operating temperature (T-T)	-10 - 85 °C
Ethernet LAN	✓	Storage temperature (T-T)	-40 - 85 °C
Ethernet interface type	Gigabit Ethernet, 2.5 Gigabit Ethernet, 4 Gigabit Ethernet	Operating relative humidity (H-H)	0 - 95%
Networking standards	IEEE 802.3	Storage relative humidity (H-H)	0 - 95%
Auto MDI/MDI-X	✓	Weight & dimensions	
Digital Diagnostics Monitoring (DDM)	✓	Width	13.4 mm
Wavelength-division multiplexing (WDM)	✗	Depth	56.5 mm
Features		Height	8.5 mm
Product colour	Silver	Weight	20 g
Housing material	Metal	Packaging data	
Plug and Play	✓	Number of products included	1 pc(s)
Hot-Plug support	✓	Package type	Box
Hot-swap	✓	Technical details	
Easy to install	✓	Sustainability compliance	✓
Country of origin	China	Sustainability certificates	RoHS
Brand compatibility	Avago Technologies	Doesn't contain	Lead



5056468759450

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.

Publication date: 26-JAN-2024. Prints or copies of Information are only valid on the printed Publication date