

# Type 3AB

## Fast Blow Fuse Series

**HF** **Pb** 3AB Series, 6x32mm Ceramic Tube Fast Blow Fuse

RoHS Compliant

### Description

6x32mm Fast Blow, Ceramic tube body cartridge fuse designed, approved and complied with UL and CSA standard 248-14.

### Features

- Meet UL and CSA standard 248-14
- Wide operating temperature range
- Bulk packing available
- Full compliance with EU Directive 2011/65/EU and amending directive 2015/863
- Halogen Free
- Lead Free

### Applications

Provide individual protection for components or internal circuits.

- Power supplies
- Battery charger
- Monitor
- Adapter

LEAD FREE = **Pb**  
 HALOGEN FREE = **HF**



### Physical Specifications

Materials	Body : Ceramic
	Cap : Nickel Plated Brass Caps
	Leads : Matte Tin Plated Copper
Marking	On Fuse :
	"bel", "3AB", "Current Rating", "Voltage Rating",
	"Appropriate Safety Logos", "✓" ( RoHS compliant)
	On Label :
	"bel", "3AB", "Current Rating", "Voltage Rating", "Interrupting Rating", "Appropriate Safety Logos" and "✓", "Pb", "E" (China RoHS compliant).

### Electrical Characteristics (UL/CSA STD.248-14) Safety Agency Approvals

Testing Current	Blow Time		Amp Range
	Minimum	Maximum	
100%	4 hrs.	N/A	100mA-20A
135%	N/A	1 hr.	100mA-10A
200%	N/A	5 sec	100mA-10A
	N/A	120 sec	12A-20A




Safety Agency	Safety Agency Certificate	Ampere Rating/ Voltage Rating	Ampere Range / Volt @ I.R. ability*
<b>UL</b> US	E20624	500mA-20A /250V AC	500mA-1A/250V AC@35A >1A-3.5A/250V AC@100A >3.5A-10A/250V AC@200A 500mA-10A/125V AC@10,000A
<b>SP</b>	LR39772		
<b>UL</b> US	E20624		
<b>PSE</b>	JET1037-31003-1010 JET1037-31003-1011		1A-5A/125V AC@500A
	JET1037-31003-1007		>5A-15A/125V AC@300A

\*I.R.= Interrupting Rating = Short Circuit Rating(Amps)

## Environmental Specifications

Shock Resistance	MIL-STD-202G, Method 213B, Test Condition 1 (100 G's peak for 6 milliseconds; Sawtooth waveform)
Vibration Resistance	MIL-STD-202G, Method 201A (10-55 Hz, 0.06 inch, total excursion).
Salt Spray Resistance	MIL-STD-202G, Method 101E, Test Condition B (48 hrs).
Insulation Resistance	MIL-STD-202G, Method 302, Test Condition A (After Opening) 10,000 ohms minimum.
Solderability	MIL-STD-202G, Method 208H
Resistance to solder Heat	MIL-STD-202G, Method 210F, Test Condition B (260+/-5°C, 10+/-1 sec)
Thermal Shock	MIL-STD-202G, Method 107G, Test Condition B (-65°C to +125°C).
Operating Temperature	-55°C to +125°C
Terminal Strength	IEC-68-2-21

## Electrical Specifications

Catalog Number	Ampere Rating	Typical Cold Resistance (ohms)	Volt-drop @100%In (Volt) max.	Voltage and Interrupting Ratings	Melting I²T <10 mSec (A² Sec)	Melting I²T @10 In (A² Sec)	Maximum Power Dissipation (W)	Agency Approvals		
										
3AB 500-R	500mA	0.74	1.50	See Table of Safety Approvals on Page 1 for Voltage and associated Interrupting Ratings	0.14	0.10	1.92	Y	Y	
3AB 750-R	750mA	0.257	0.36		0.75	0.74	0.30	Y	Y	
3AB 1-R	1A	0.155	0.28		1.4	1.4	0.37	Y	Y	Y
3AB 1.25-R	1.25A	0.114	0.27		2.5	2.5	0.44	Y	Y	Y
3AB 1.5-R	1.5A	0.089	0.27		3.80	3.95	0.49	Y	Y	Y
3AB 1.6-R	1.6A	0.085	0.27		4.2	4.4	0.51	Y	Y	Y
3AB 2-R	2A	0.057	0.22		7.2	7.6	0.59	Y	Y	Y
3AB 2.5-R	2.5A	0.043	0.21		12	13	0.70	Y	Y	Y
3AB 3-R	3A	0.033	0.17		21	23	0.83	Y	Y	Y
3AB 3.5-R	3.5A	0.027	0.18		28	31	0.91	Y	Y	Y
3AB 4-R	4A	0.024	0.17		36	40	1.00	Y	Y	Y
3AB 5-R	5A	0.018	0.16		63	70	1.20	Y	Y	Y
3AB 6-R	6A	0.014	0.15		107	123	1.40	Y	Y	Y
3AB 7-R	7A	0.012	0.16		141	162	1.60	Y	Y	Y
3AB 8-R	8A	0.010	0.15		184	214	1.70	Y	Y	Y
3AB 10-R	10A	0.008	0.13		316	372	2.00	Y	Y	Y
3AB 12-R	12A	0.009	0.19		501	597	2.30	Y		Y
3AB 15-R	15A	0.007	0.17		845	1023	2.70	Y		Y
3AB 20-R	20A	0.004	0.15		1598	1968	3.00	Y		

Consult manufacturer for other ratings




Specifications subject to change without notice


**Bel Fuse Inc.**  
206 Van Vorst Street  
Jersey City, NJ 07302 USA

+1 201.432.0463  
Bel.US.CS@belf.com  
[belfuse.com/circuit-protection](http://belfuse.com/circuit-protection)

## Temperature Derating Curve




## Average Time Current Curve



## Soldering Parameters

Lead-free Wave Soldering Profile	
Wave Soldering Parameter	
Average ramp-up rate	200°C / second
Heating rate during preheat	typical 1 - 2°C / second Max 4°C / second
Final preheat temperature	within 125°C of soldering temperature
Peak temperature Tp	260°C
Time within +0°C / -5°C of actual peak temperature	10 seconds
Ramp-down rate	5°C / second max.



## Fuse FGNO Explanation


06X3 R [XXXX] -XX

0603R=3AB; [XXXX]=Ampere Rating; XX=See Ordering Information as below


Fraction	Decimal	Milliamps	Bel FGNO[XXXX]
1/2	.500	500	0500
3/4	.750	750	0750

Fraction	Decimal	Amps	Bel FGNO[XXXX]
	1.0	1	1000
1-1/4	1.25	1.25	1250
1-1/2	1.50	1.5	1500
	1.60	1.6	1600
	2.0	2	2000
2-1/2	2.5	2.5	2500
	3.0	3	3000
3-1/2	3.5	3.5	3500
	4.0	4	4000
	5.0	5	5000
	6.0	6	6000
	7.0	7	7000
	8.0	8	8000
		10	9100
		12	9120
		15	9150
		20	9200

## Mechanical Dimensions



## Ordering Information



## Packaging

Packaging Option	Packaging Specification	Quantity	Packaging Code	Inside Tape Spacing
Bulk	N/A	1000	33	N/A