

3A, 50V - 1000V High Efficient Surface Mount Rectifier

FEATURES

- AEC-Q101 qualified
- Glass passivated chip junction
- Ideal for automated placement
- Low forward voltage drop
- Low profile package
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- DC to DC converter
- Automotive application
- Car lighting
- Snubber
- Freewheeling application

MECHANICAL DATA

- Case: DO-214AB (SMC)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.210g (approximately)

KEY PARAMETERS				
PARAMETER	VALUE	UNIT		
I _F	3	Α		
V_{RRM}	50 - 1000	V		
I _{FSM}	150	Α		
T _{J MAX}	150	°C		
Package	DO-214AB (SMC)			
Configuration	Single die			









DO-214AB (SMC)



PARAMETER	SYMBOL	HS	HS	HS	HS	HS	HS	HS	HS	UNIT
		3AH	ан звн	3DH	3FH	3GH	ЗЈН	3KH	ЗМН	UNII
Marking code on the device		HS3A	HS3B	HS3D	HS3F	HS3G	HS3J	HS3K	HS3M	
Repetitive peak reverse voltage	V_{RRM}	50	100	200	300	400	600	800	1000	V
Reverse voltage, total rms value	V _{R(RMS)}	35	70	140	210	280	420	560	700	V
Forward current	I _F	3			Α					
Peak forward surge current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	150			А					
Junction temperature	TJ	- 55 to +150			°C					
Storage temperature	T _{STG}	- 55 to +150			°C					



THERMAL PERFORMANCE				
PARAMETER	SYMBOL	TYP	UNIT	
Junction-to-ambient thermal resistance	$R_{\Theta JA}$	60	°C/W	

PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
(1)	HS3AH HS3BH HS3DH HS3FH	I _F = 3A, T _J = 25°C		-	1.0	V
Forward voltage ⁽¹⁾	HS3GH		V _F	-	1.3	V
	HS3JH HS3KH HS3MH			-	1.7	V
Reverse current @ rated V _R ⁽²⁾		T _J = 25°C		-	10	μA
		T _J = 125°C	- I _R	-	250	μA
Junction capacitance	HS3AH HS3BH HS3DH HS3FH HS3GH	1MHz, V _R = 4.0V	С	80	-	pF
	HS3JH HS3KH HS3MH			50	-	pF
Reverse recovery time	HS3AH HS3BH HS3DH HS3FH HS3GH	$I_F = 0.5A, I_R = 1.0A,$ $I_{rr} = 0.25A$	t _{rr}	-	50	ns
	HS3JH HS3KH HS3MH			-	75	ns

Notes:

- 1. Pulse test with PW = 0.3ms
- 2. Pulse test with PW = 30ms

ORDERING INFORMATION				
ORDERING CODE ⁽¹⁾	PACKAGE	PACKING		
HS3xH	DO-214AB (SMC)	3,000 / Tape & Reel		

Notes:

1. "x" defines voltage from 50V(HS3AH) to 1000V(HS3MH)



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.1 Forward Current Derating Curve




Fig.3 Typical Reverse Characteristics





Fig.2 Typical Junction Capacitance

Fig.4 Typical Forward Characteristics







Fig.5 Maximum Non-Repetitive Forward Surge Current



NUMBER OF CYCLES AT $60\ Hz$





Taiwan Semiconductor

CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$

Fig.6 Reverse Recovery Time Characteristic and Test Circuit Diagram











PACKAGE OUTLINE DIMENSIONS


DO-214AB (SMC)





DIM. Unit		(mm)	Unit ((inch)
Dilvi.	Min.	Max.	Min.	Max.
Α	2.00	2.62	0.079	0.103
A1	0.10	0.20	0.004	0.008
b	2.90	3.20	0.114	0.126
С	0.15	0.31	0.006	0.012
D	5.59	6.22	0.220	0.245
E	7.75	8.13	0.305	0.320
E1	6.60	7.11	0.260	0.280
L	1.00	1.60	0.039	0.063

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
Α	3.30	0.130
В	2.50	0.098
С	6.90	0.272
D	4.40	0.173
E	9.40	0.370

MARKING DIAGRAM



P/N = Marking Code G = Green Compound

ΥW = Date Code F = Factory Code



Taiwan Semiconductor

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.