

TPSMF4L Series

Surface Mount – 400W



Additional Information



Resources



Accessories



Samples

Agency Approvals

| Agency | Agency File Number |
|--------|--------------------|
| | E230531 |

Maximum Ratings and Thermal Characteristics


($T_A=25^\circ\text{C}$ unless otherwise noted)

| Parameter | Symbol | Value | Unit |
|---|-----------------|-----------|--------------------|
| Peak Pulse Power | P_{PPM} | 2000 | W |
| Dissipation at $T_A=25^\circ\text{C}$ | | 400 | W |
| Power Dissipation On Infinite Heat Sink at $T_L=50^\circ\text{C}$ | P_D | 1 | W |
| Thermal Resistance Junction to Ambient | $R_{\theta JA}$ | 220 | $^\circ\text{C/W}$ |
| Thermal Resistance Junction to Lead | $R_{\theta JL}$ | 100 | $^\circ\text{C/W}$ |
| Operating and Storage Temperature Range | T_J, T_{STG} | -55 - 150 | $^\circ\text{C}$ |

Notes:

- Non-repetitive current pulse, per Fig. 4 and derated above T_J (initial) $=25^\circ\text{C}$ per Fig. 3.
- TPSMF4L5.0A-TPSMF4L8.5A Peak Pulse Power Dissipation is 1850W min, 2000W typical @8/20us
- TPSMF4L5.0A-TPSMF4L8.5A Peak Pulse Power Dissipation is 370W min, 400W typical @10/1000us

Functional Diagram



Description

The TPSMF4L series of SOD-123FL small and flat lead low-profile plastic package is designed specifically to protect sensitive electronic equipment from voltage transients induced by lightning and other transient voltage events, and it's especially suitable for high reliability and automotive application.

Features

- High reliability application and automotive grade AEC-Q101 qualified
- 400W peak pulsepower capability at 10/1000us waveform, repetition rate (duty cycle): 0.01 %
- Compatible with industrial standard package SOD-123FL
- Low inductance, excellent clamping capability
- For surface mounted applications to optimize board space
- Typical failure mode is short from over-specified voltage or current
- Whisker test is conducted based on JEDEC JESD201A per its table 4a and 4c
- IEC 61000-4-2 ESD 30kV(Air), 30kV (Contact)
- ESD protection of data lines in accordance with IEC 61000-4-2
- EFT protection of data lines in accordance with IEC 61000-4-4
- Fast response time: typically less than 1.0ns from 0 Volts to VBR min
- High temperature soldering: $260^\circ\text{C}/30$ seconds at terminals
- $V_{BR} @ T_J = V_{BR} @ 25^\circ\text{C} \times (1 + \alpha T \times (T_J - 25))$ (αT : Temperature Coefficient, typical value is 0.1 %)
- Glass passivated junction
- Built-in strain relief
- Plastic package is flammability rated V-0 per Underwriters Laboratories
- Meet MSL level1, per J-STD-020, LF maximum peak of 260°C
- Matte tin lead-free plated
- Halogen-free and RoHS compliant
- Pb-free E3 means 2nd level interconnect is Pb-free and the terminal finish material is tin(Sn) (IPC/JEDEC J-STD-609A.01)
- UL Recognized as an Isolated Loop Circuit Protector per UL 497B

Applications

TPSMF4L devices are ideal for the protection of portable devices/ hard drives, notebooks, VCC busses, POS terminal, SSDs, power supplies, monitors, and vulnerable circuit used in other consumer applications.

TPSMF4L Series

Surface Mount – 400W

Electrical Characteristics ($T_A=25\text{ }^\circ\text{C}$ unless otherwise noted)

| Part Number | Marking Code | Breakdown Voltage V_{BR} (Volts) @ I_T | | Test Current I_T (mA) | Reverse Stand off Voltage V_R (V) | Maximum Reverse Leakage @ V_R, I_R (μA) | Maximum Peak Pulse Current I_{PP} (A) | Maximum Clamping Voltage @ I_{PP}, V_C (V) | Agency Approval |
|-------------|--------------|--|--------|-------------------------|-------------------------------------|--|---|--|-----------------|
| | | Min | Max | | | | | | |
| TPSMF4L5.0A | KEA | 6.40 | 7.00 | 10 | 5.0 | 800 | 40.1 | 9.2 | X |
| TPSMF4L6.0A | KGA | 6.67 | 7.37 | 10 | 6.0 | 800 | 35.9 | 10.3 | X |
| TPSMF4L6.5A | KKA | 7.22 | 7.98 | 10 | 6.5 | 500 | 33.1 | 11.2 | X |
| TPSMF4L7.0A | KMA | 7.78 | 8.60 | 10 | 7.0 | 200 | 30.9 | 12.0 | X |
| TPSMF4L7.5A | KPA | 8.33 | 9.21 | 1 | 7.5 | 100 | 28.7 | 12.9 | X |
| TPSMF4L8.0A | KRA | 8.89 | 9.83 | 1 | 8.0 | 50 | 27.2 | 13.6 | X |
| TPSMF4L8.5A | KTA | 9.44 | 10.40 | 1 | 8.5 | 20 | 25.7 | 14.4 | X |
| TPSMF4L9.0A | KVA | 10.00 | 11.10 | 1 | 9.0 | 5 | 26.4 | 15.4 | X |
| TPSMF4L10A | KXA | 11.10 | 12.30 | 1 | 10 | 5 | 23.5 | 17.0 | X |
| TPSMF4L11A | KZA | 12.20 | 13.50 | 1 | 11 | 1 | 22.0 | 18.2 | X |
| TPSMF4L12A | LEA | 13.30 | 14.70 | 1 | 12 | 1 | 20.1 | 19.9 | X |
| TPSMF4L13A | LGA | 14.40 | 15.90 | 1 | 13 | 1 | 18.6 | 21.5 | X |
| TPSMF4L14A | LKA | 15.60 | 17.20 | 1 | 14 | 1 | 17.2 | 23.2 | X |
| TPSMF4L15A | LMA | 16.70 | 18.50 | 1 | 15 | 1 | 16.4 | 24.4 | X |
| TPSMF4L16A | LPA | 17.80 | 19.70 | 1 | 16 | 1 | 15.4 | 26.0 | X |
| TPSMF4L17A | LRA | 18.90 | 20.90 | 1 | 17 | 1 | 14.5 | 27.6 | X |
| TPSMF4L18A | LTA | 20.00 | 22.10 | 1 | 18 | 1 | 13.7 | 29.2 | X |
| TPSMF4L20A | LVA | 22.20 | 24.50 | 1 | 20 | 1 | 12.3 | 32.4 | X |
| TPSMF4L22A | LXA | 24.40 | 26.90 | 1 | 22 | 1 | 11.3 | 35.5 | X |
| TPSMF4L24A | LZA | 26.70 | 29.50 | 1 | 24 | 1 | 10.3 | 38.9 | X |
| TPSMF4L26A | MEA | 28.90 | 31.90 | 1 | 26 | 1 | 9.5 | 42.1 | X |
| TPSMF4L28A | MGA | 31.10 | 34.40 | 1 | 28 | 1 | 8.8 | 45.4 | X |
| TPSMF4L30A | MKA | 33.30 | 36.80 | 1 | 30 | 1 | 8.3 | 48.4 | X |
| TPSMF4L33A | MMA | 36.70 | 40.60 | 1 | 33 | 1 | 7.5 | 53.3 | X |
| TPSMF4L36A | MPA | 40.00 | 44.20 | 1 | 36 | 1 | 6.9 | 58.1 | X |
| TPSMF4L40A | MRA | 44.40 | 49.10 | 1 | 40 | 1 | 6.2 | 64.5 | X |
| TPSMF4L43A | MTA | 47.80 | 52.80 | 1 | 43 | 1 | 5.8 | 69.4 | X |
| TPSMF4L45A | MVA | 50.00 | 55.30 | 1 | 45 | 1 | 5.5 | 72.7 | X |
| TPSMF4L48A | MXA | 53.30 | 58.90 | 1 | 48 | 1 | 5.2 | 77.4 | X |
| TPSMF4L51A | MZA | 56.70 | 62.70 | 1 | 51 | 1 | 4.9 | 82.4 | X |
| TPSMF4L54A | NEA | 60.00 | 66.30 | 1 | 54 | 1 | 4.6 | 87.1 | X |
| TPSMF4L58A | NGA | 64.40 | 71.20 | 1 | 58 | 1 | 4.3 | 93.6 | X |
| TPSMF4L60A | NKA | 66.70 | 73.70 | 1 | 60 | 1 | 4.1 | 96.8 | X |
| TPSMF4L64A | NMA | 71.10 | 78.60 | 1 | 64 | 1 | 3.9 | 103.0 | X |
| TPSMF4L70A | NPA | 77.80 | 86.00 | 1 | 70 | 1 | 3.5 | 113.0 | X |
| TPSMF4L75A | NRA | 83.30 | 92.10 | 1 | 75 | 1 | 3.3 | 121.0 | X |
| TPSMF4L78A | NTA | 86.70 | 95.80 | 1 | 78 | 1 | 3.2 | 126.0 | X |
| TPSMF4L85A | NVA | 94.40 | 104.00 | 1 | 85 | 1 | 2.9 | 137.0 | X |


Notes:

- V_{BR} measured after I_T applied for 300 μs . I_T = square wave pulse or equivalent.
- Surge current waveform per 10/1000 μs exponential wave and derated per Fig.3.
- All terms and symbols are consistent with ANSI/IEEE C62.35.

TPSMF4L Series

Surface Mount – 400W

I-V Curve Characteristics



- P_{PPM} **Peak Pulse Power Dissipation** – Max power dissipation
- V_R **Stand-off Voltage** – Maximum voltage that can be applied to the TVS without operation
- V_{BR} **Breakdown Voltage** – Maximum voltage that flows through the TVS at a specified test current (I_r)
- V_C **Clamping Voltage** – Peak voltage measured across the TVS at a specified I_{ppm} (peak impulse current)
- I_r **Reverse Leakage Current** – Current measured at V_R
- V_f **Forward Voltage Drop for Uni-directional**

Ratings and Characteristic Curves ($T_A=25\text{ }^\circ\text{C}$ unless otherwise noted)

Figure 1 -
TVS Transients Clamping Waveform





Figure 2 -
Peak Pulse Power Rating Curve



TPSMF4L Series

Surface Mount – 400W

Ratings and Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted) (Continued)

Figure 3 -
Peak Pulse Power Derating Curve




Figure 4 -
Pulse Waveform - 10/1000 μs




Figure 5 -
Forward Voltage




Figure 6 -
Typical Junction Capacitance




Figure 7 -
Peak Forward Voltage Drop vs. Peak Forward Current





Figure 8 -
Maximum Non-Repetitive Forward Surge Current Uni-Directional Only




TPSMF4L Series

Surface Mount – 400W

Soldering Parameters

| | | |
|--|------------------------------------|-------------------------|
| Reflow Condition | | Lead-free assembly |
| Pre Heat | - Temperature Min ($T_{s(min)}$) | 150°C |
| | - Temperature Max ($T_{s(max)}$) | 200°C |
| | - Time (min to max) (t_g) | 60 – 120 secs |
| Average ramp up rate (Liquidus Temp (T_L) to peak) | | 3°C/second Max |
| $T_{s(max)}$ to T_L - Ramp-up Rate | | 3°C/second Max |
| Reflow | - Temperature (T_L) (Liquidus) | 217°C |
| | - Time (min to max) (t_L) | 60 – 150 seconds |
| Peak Temperature (T_p) | | 260 ^{+0/-5} °C |
| Time within 5°C of actual peak Temperature (t_p) | | 30 seconds Max |
| Ramp-down Rate | | 6°C/second Max |
| Time 25°C to peak Temperature (T_p) | | 8 minutes Max. |
| Do not exceed | | 260°C |




Physical Specifications

| | |
|-----------------|--|
| Case | SOD-123FL plastic over glass passivated junction |
| Polarity | Color band denotes cathode except bipolar |
| Terminal | Matte tin-plated leads, solderable per JESD22-B102 |


Environmental Specifications

| | |
|----------------------------|--------------------------|
| High Temp. Storage | JESD22-A103 |
| HTRB | JESD22-A108 |
| Temperature Cycling | JESD22-A104 |
| MSL | JEDEC-J-STD-020, Level 1 |
| H3TRB | JESD22-A101 |
| RSH | JESD22-A111 |

Dimensions - SOD-123FL Package



Mounting Pad Layout




| Dimensions | Millimeters | | Inches | |
|------------|-------------|------|--------|-------|
| | Min | Max | Min | Max |
| A | 2.90 | 3.10 | 0.114 | 0.122 |
| B | 3.50 | 3.90 | 0.138 | 0.154 |
| C | 0.85 | 1.05 | 0.033 | 0.041 |
| D | 1.70 | 2.00 | 0.067 | 0.079 |
| E | 0.43 | 0.83 | 0.017 | 0.033 |
| F | 0.10 | 0.25 | 0.004 | 0.010 |
| G | 0.00 | 0.10 | 0.000 | 0.004 |
| H | 0.90 | 1.08 | 0.035 | 0.043 |


TPSMF4L Series

Surface Mount – 400W

Part Numbering System




Part Marking System



Packaging Options

| Part number | Component Package | Quantity | Packaging Option | Packaging Specification |
|-------------|-------------------|----------|--------------------------------|-------------------------|
| TPSMF4LXXX | SOD-123FL | 3000 | Tape & Reel – 8mm tape/7" reel | EIA RS-481 |

Tape and Reel Specification



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at <http://www.littelfuse.com/disclaimer-electronics>.