

DESCRIPTION: 3W3 // F // COAXIAL // RA PCB MOUNT





SPECIFICATIONS:

ELECTRICAL:

INSULATOR RESISTANCE: 5 GOHMS Min.
DIELECTRIC WITHSTANDING: 1,000VAC r.m.s.
OPERATING TEMPERATURE: -55° C ~ +125° C
COAXIAL CONTACT RESISTANCE: 2.7 MilliOHMS Max.
COAXIAL IMPEDANCE: 50 OHM

MECHANICAL:

CONTACT INSERTION FORCE: 4.5 Kg Max. CONTACT SEPARATOR FORCE: 0.3 Kg Min.

MATERIALS:

CONTACTS: COPPER ALLOY INSULATOR: PBT UL94V-0 RATED,

BLACK

230°C PROCESS TEMP.

SHELL: STEEL

FINISH:

SHELL: NICKEL

CONTACTS: FULL GOLD FLASH

685M3W3203L461

46 = 4-40 INSERTS / BOARD LOCKS

REV

2

ROHS COMPLIANT

体

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NOrComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

DATE:

M. SIGMON

02/27/2015

UNITS = INCHES [MM] DO NOT SCALE FROM DRAWING




SCALE: SHEET 1


DWG NO: 00 5140044

685M3W3203L461

OF

2





ROHS COMPLIANT

及

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE: 02/27/2015

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	SHEET		OF			REV
NTS		2		2		2
owg no:	85M3	3W:	320	3L4	461	