


REVISIONS								
REV.	DESCRIPTION	DATE	APPROVED					
Α	REDRAWN ON NEW FORMAT	12/8/2014	D.N.					



NOTES:

MATERIALS:

1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B". 2. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-01, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

 2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-01, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER MIL-C-14550.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 12/08/14 DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior a RADIALL company written permission of RADIALL.				
DECIMAL	DECIMAL ANGLE		N.D. 12/08/14 APVD: DATE SMB			STRAIGHT MALE JACK CLAMP TYPE G-316 & SIMILAR CABLES		
REFERENCE: ORIGINATED: D.N.		MATERIALS & FINISHES: SEE NOTES		size A	FSCM NO. 19505	DWG NO. 2001-155	51-003	REV A
DATE: 12/08/14				SCALE	7:1	THIRD ANGLE PROJECTION	SHEET 1 C)F 1