


REVISIONS								
REV.	DESCRIPTION	DATE	APPROVED					
А	INITIAL RELEASE	04/16/18	C.E.					



NOTES:

MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 2. LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 3. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.
 ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: DATE C.E. 04/16/1	communicated to a third party without prior				
		CHKD: DATE	a RADIALL companywritten permission of RADIALL.				
DECIMAL	ANGLE	D.N. 04/16/1					
APVD: DATE RECESSED PRESS IN		PRESS IN FROM	1UOM TI	NT			
		J.M. 04/16/1	8		RECEPTACLE		
REFERENCE:		MATERIALS & FINISHES:	SIZE A	FSCM NO. 19505	DWG NO. 3014-1511	-000	rev A
ORIGINATED: C.E. DATE: 04/16/18		SEE NOTES	SCALE	5:1	THIRD ANGLE PROJECTION	SHEET 1 O	F 1