

Environment Sensing Board

NO.EEV-576-211118

1. Overview


The RIOT-001, an environment sensing board, transmits data obtained from a temperature/humidity and pressure sensor (BME280) and an ambient light sensor (MAX44009) to tablets or other smart devices by using Bluetooth Low Energy (BLE). It can operate with a solar battery panel for indoor light*1.

The electric power a solar battery panel generates is harvested efficiently by the R1800, a buck DC/DC converter for energy harvest, and stored in a small Li-ion secondary battery. The stored power is supplied to a BLE module with an MCU and sensors by the RP604, an ultra-low supply current buck-boost DC/DC converter.

The board also includes the RP124, a voltage regulator with a battery monitor, to monitor the secondary battery voltage. By transmitting battery information to tablets or other smart devices via an AD converter inside the BLE module, it is possible to check the state of the secondary battery voltage.

2. Board Specifications

2-1. Block Diagram



^{*1} Solar battery panels are not provided with the board.

2-2. Ratings

| Symbol | Parameter | Condition | Min. | Тур. | Max. |
|--------|------------------------------------|-----------------|--------|------------|--------|
| Vin | Input Voltage | | 2.0 V | - | 5.5 V |
| Vmp | Max. Power Voltage | | | 4.4 V | |
| Vout | Output Voltage | | 1.79 V | 2.0 V | 2.03 V |
| Vlib | Secondary Battery Charging Voltage | | 2.62 V | 2.7 V | 2.78 V |
| Icc | Avg. Operating Current | | | 16.4 uA *2 | |
| Та | Operating Temperature | No condensation | 0°C | | 50°C |

^{*2} The value refers to an average supply current when the board is used with firmware that intermittently operates once per 5 seconds.

2-3. BLE Transmission

The board contains an integrated sensor (BME280) measuring temperature, humidity and pressure, an ambient light sensor (MAX44009), and a voltage regulator with a battery monitor (RP124) for measurement of the secondary battery voltage. It calculates the measured values at BLE transmission and transmits them as BLE advertising data.

The following list shows format specifications of the BLE advertising data.

| Types | Data |
|------------------|---------------------------------------|
| Flags | 02 01 04 |
| Local Name | 06 09 ① ① ① ① ① |
| Manufacture Data | 0F FF 5B 08 00 05 2 2 3 3 4 4 5 5 6 6 |

(1)

Stores a 5-byte-long device name.

(2)

Temperature (°C). Stores a 2-byte signed datum (hexadecimal representation) determined by calculating a value to the first decimal place and multiplying it by 10.

(3)

Humidity (%RH). Stores a 2-byte unsigned datum (hexadecimal representation) determined by calculating a value to the first decimal place and multiplying it by 10.

4)

Air pressure (hPa). Stores a 2-byte unsigned datum (hexadecimal representation) determined by calculating a value to the first decimal place and multiplying it by 10.

(5)

Illuminance (Lux). Stores a 2-byte unsigned datum (hexadecimal representation) determined by dividing a calculated integral number by 4 (fractions smaller than 4 omitted).

6)

Battery voltage (V). Stores a 2-byte unsigned datum (hexadecimal representation) determined by calculating a value to the third decimal place and multiplying it by 1000.

The 2-byte data mentioned above are stored in a little-endian format.

An example of BLE advertising data is shown below: R0001, the device name; temperature at 25.2°C; humidity at 40.8%; pressure at 1012.4 hPa; illuminance at 680 Lux; battery voltage at 2.62 V.

| Types | Data |
|------------------|---|
| Flags | 02 01 04 |
| Local Name | 06 09 52 30 30 30 31 |
| Manufacture Data | OF FF 5B 08 00 05 FC 00 98 01 8C 27 AA 00 3C 0A |

BLE advertising data are broadcast once per 5 seconds*3. The transmitted information is readable with RIoT Monitor, our application for Android devices (Ver.7.0 or above).

(*3) A default value. The operation interval may vary by the firmware used with this board.

2-4. Main Parts

| Part No. | Product Name | Product No. | Vendor | Notes |
|----------|---|--------------|----------------------------|---|
| IC1 | Buck DC/DC Converter for Energy Harvest | R1800K022A | Nisshinbo Micro Devices | For power control from a solar battery panel |
| IC2 | Buck-boost DC/DC Converter | RP604K201B | Nisshinbo Micro Devices | A power supply for the BLE module, etc. |
| IC3 | Temperature, Humidity and Pressure Sensor | BME280 | BOSCH | |
| IC4 | LDO + Battery Monitor | RP124L123B | Nisshinbo Micro Devices | A battery monitor for secondary battery voltage |
| IC6 | Ambient Light Sensor | MAX44009 | MAXIM | For illuminance measurement |
| IC7 | BLE Module | RY7011A | Renesas Electronics | A BLE module including an MCU |
| B1 | Secondary Battery | SLB03070LR35 | Nichicon | SLB series ϕ 3 x 7 L (mm) |

Links to datasheets of each component are below. (*4)

R1800K022A

https://www.nisshinbo-microdevices.co.jp/en/pdf/datasheet/r1800-ea.pdf

RP604K201B

https://www.nisshinbo-microdevices.co.jp/en/pdf/datasheet/rp604-ea.pdf

RP124L123B

https://www.nisshinbo-microdevices.co.jp/en/pdf/datasheet/rp124-ea.pdf

BME280

https://www.bosch-sensortec.com/bst/products/all_products/bme280

MAX44009

https://www.maximintegrated.com/en/products/interface/sensor-interface/MAX44009.html

RY7011A


https://www.renesas.com/us/en/products/microcontrollers-microprocessors/rl78/rl78g1x/rl78g1d/device/RY7011A0000DZ00.html

SLB03070LR35

https://www.nichicon.co.jp/_assets/pdf/products/slb/en_specification1.pdf

(*4) Check the latest information on the vendors' web sites because the specifications and URLs may be updated.

2-5. Appearance



2-6. Recommended Solar Battery Panels

Amorphous silicon solar battery panels for indoor products suggested below are highly recommended.

Vendor: Panasonic Solar Amorton Co., Ltd.

Product name: AM-18xx series (open-circuit voltage: V_{OC} = 5.0 V)

Link to reference: https://panasonic.co.jp/ls/psam/en/products/

Other solar battery panels with Voc from 4.0 V to 5.5 V are also available (optimal voltage: 5.0 V).

The terminals of the solar battery panel must be connected to the terminals of the board by such as soldering, etc.

2-7. Power Supply Switch

Slide the power supply switch to the ON printed on the board, and the board will start the operation as an environmental sensor by providing the BLE module and the sensors with electricity.



- The products and product specifications described in this document are subject to change or discontinuation of production without notice for reasons such as improvement. Therefore, before deciding to use the products, Customer shall refer to our sales representatives for the latest information thereon.
- The information contained in this document is carefully prepared for accuracy, but does not warrant that there will be no mistakes. Please note that our company is not 2. responsible for any damage to customers caused by any errors or inaccuracies in this document.
 - The information contained in this document is presented only as examples and guidance of product use. Please note that our company assumes no liability for any
- damage to customers caused by use of the products. 3. Customers shall be solely responsible for all aspects of their own product-design and applications in use of the circuit, software or related information described in this document: design including the products or incorporation of the products into their own applications. In this regard, customers must provide shipping inspections to ensure design for safety such as redundancy, anti-failure and fire containment. Aging process is also necessary to ensure customers' design standard for safety
 - The technical information described in this document shows typical characteristics and examples of application circuits for the products.
- The release of such information does not guarantee a grant of license of our company's or any third party's intellectual property rights or any other rights related to the products including combination with any other products
 - The materials in this document may not be copied or otherwise reproduced in whole or in part without prior written consent of us.
- In the event that any product or related technology described in this document falls under the category of products controlled under Foreign Exchange and Foreign Control
- Trade Law, exporting of such products or technology shall require an export license from the Japanese government in accordance with the above law
- The products and technology shall not be used for any products or systems of which manufacturing or sales is prohibited under any applicable laws or regulations.
- The certification labels, including the technical conformity mark validated by Japan Radio Act, are on the surface of the RL78/G1D module. Please follow the radio wave 8.
- regulation of the country where this product is used.
 - Our company is not responsible for damage caused by failure to properly follow the recommended operating conditions or product specifications described in this
- 9. document.
- 10. Customer shall not disassemble, analyze, reverse-engineer, alter, modify or the like the products, whether in whole or in part. In case of the above, we does not warrant the products
- Our company does not warrant functional characteristics and performance depending on the software made by customers.
- Our company does not warrant interconnectivity and/or compatibility between the products and components except for the recommended components described in this 12.
- All the information contained in this document is applied to only the products purchased through proper channels such as our sales representatives. 13.
 - Please note that our warranty does not cover free samples and products purchased via another channels
- This product is a sample board for customers to understand our power management ICs. Safety, reliability, compatibility, etc., which are commonly required by final 14. products for consumers or industries, are not considered in design, nor in sales, nor in manufacturing.
 - Please note that we do not take any responsibility or liability for any damage or loss using the product for any final products for consumer or industry
- Customers shall be strictly prohibited to use the products in equipment or systems that require extreme level of quality and reliability, and of which malfunction or failure may cause loss of human life and/or bodily injury, e.g., equipment used in aerospace industry, nuclear reactor control systems, traffic control systems, automotive and transportation equipment, combustion equipment, safety devices, life support systems.
- Customer shall not use the products under any of the conditions mentioned bellow. This may cause malfunction or defect. 16.

in high humidity

under oily environment

in corrosive atmosphere

under environment with corrosive gas or inflammable gas

under an extremely high or low temperature environment

under conditions of violent vibration

in the place that generates electrostatic charges and electrifies

in a place that exposed to direct sunlight

in a dusty place

- Anti-radiation design is not implemented in the products described in this document.
- 17. Improper or unintended use or misuse may lead to loss of human life and bodily injury, firing and smoking, failure of the products and connected components, and damage to property or loss of social profits.
- 18. Sharp edge of components such as short plug may unavoidably appear. Customer shall handle the products with the utmost care and attention to avoid injury from the
- To avoid electrostatic discharge failure, Customer shall not touch the metal portion of the connector with bare hands or fingers. 19.
 - Also, Customer shall remove static electricity of the human body before handling the products through touching something made of metal such as door handles. Customer shall turn off immediately when firing, smoking or abnormal heating occur during operation.
- 20. When connecting the products to other products, Customer shall not give excessive stress on the products. Customer shall not warpage boards nor push forcefully the 21. mounted components
- 22. Customer shall not apply the supply voltage to the product if the surface of the board is wet or the product touches any metals.
- The X-ray exposure can influence functions and characteristics of the products. 23
- Do not turn on this product at the place where using wireless devices is prohibited, such as in airplanes, hospitals, near an implantable cardiac pacemaker or medical 24. electrical equipment, etc.
 - The radio wave generated from this product may interfere with those devices' operation.
- 25. This product may be affected by radio waves emitted from devices or equipment such as wireless LAN, BLE devices, digital cordless phones, microwave ovens, etc.
- This product must not be incorporated nor used in a metallic cabinet. Also, do not use cabinets whose coating materials contain metal composition 26.
- Our company warrants the products with exceptions as indicated below, to the original purchaser to be free of defects for a period of three months from the date of arrival. 27. Within the warranty period, we will replace a defective product with a substitute. We assumes no liability for indirect, special or incidental damage or loss including loss of profits and consequential damage regardless of possibility of anticipation.



Nisshinbo Micro Devices Inc.

Official website

https://www.nisshinbo-microdevices.co.jp/en/

Purchase information

https://www.nisshinbo-microdevices.co.jp/en/buy/