



ROHS COMPLIANT

PRODUCT DATA DRAWING









MATERIAL:

BODY & INSERT: STAINLESS STEEL

CONTACT: **BERYLLIUM COPPER**

INSULATOR: ULTEM 1000

FINISH:

BODY & INSERT: PASSIVATED

CONTACT: **GOLD OVER NICKEL**

PERFORMANCE:

IMPEDANCE: 50 OHMS FREQ. RANGE: DC TO 50.0 GHz MATERIAL: **SEE NOTES** FINISH: SEE NOTES SURFACE AREA: N/A **PROPRIETARY** THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING,
3) BREAK CORNERS & EDGES 005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63-MIL-STD-10.
6) DIA:'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN T.I.R.
7) REMOVE ALL BURRS

DRAWN: SJ 11/13/20 CHECKED: STW 11/13/20 APPROVED: STW 11/13/20

MICROWAVE

2.4 mm JACK 4-HOLE FL. MT. ACCEPTS Ø.012±.0005 PIN

SIZE DWG. NO. 1621-60072

SCALE: 8:1