


Rev. V3

Features

- Non-Magnetic Package Suitable for MRI Applications
- Rectangular MELF SMQ Ceramic Package
- Hermetically Sealed
- Low Rs for Low Series Loss
- Long τ_L for Lower Intermodulation Distortion
- ♦ Low C_i for High Series Isolation
- High Average Incident Power Handling
- RoHS Compliant



Diode Cross Section

1072

Description

The MA4P7464F-1072T is a surface mountable PIN diode in a non-magnetic, Metal Electrode Leadless Faced (MELF) package. The device incorporates M/A-COM Technology Solutions time proven HIPAX technology to produce a low inductance ceramic package with no ribbons or whisker wires. Incorporated in the package is a hard glass passivated, CERMACHIP™ PIN chip that is full face bonded on both the cathode and anode to maximize surface area for the lowest electrical and thermal resistance. The package utilizes a nonmagnetic plating process that provides for a package with extremely low permeability. MA4P7464F-1072T has been comprehensively characterized both electrically and mechanically to ensure repeatable and predictable performance. The non-magnetic MA4P7464F-1091T is the electrical equivalent of its magnetic counterpart the MA4P7004F-1072T.

Applications

This diode is well suited for use in low loss, low distortion, high power switching circuits and can be used in high magnetic field environments at HF through UHF frequencies. The low thermal resistance of this device provides excellent performance at high RF power incident levels, up to 100 watts CW. This device is designed to meet the most demanding electrical and mechanical MRI environments.

Designed for Automated Assembly

These SMQ PIN diodes are designed for high volume tape and reel assembly. The rectangular package design provides for highly efficient automatic pick and place assembly techniques. The parallel flat surfaces are suitable for key jaw or vacuum pickup. All solderable surfaces are tin plated and compatible with reflow and vapor phase soldering methods.

Absolute Maximum Ratings¹ @ 25°C

Parameter	Absolute Maximum	
Operating Temperature	-65 °C to +125°C	
Storage Temperature	-65 °C to +150°C	
Diode Junction Temperature	+175 °C Continuous	
Diode Mounting Temperature	+265°C for 10 seconds	
RF C.W. Incident Power	+ 50 dBm C.W.	
Forward D.C. Current	+ 250 mA	
Reverse D.C. Voltage @ -10uA	I - 400 V I	

^{1.} Exceeding these limits may cause permanent damage.



Rev. V3

Electrical Specifications @ +25 °C

Parameter	Symbol	Condition	Unit Value
Forward Voltage (Maximum)	V _F	I _F = +100 mA	1.0 V _{DC}
Voltage Rating (Minimum)	V _R	Ir = -10 uA	I – 400 I V _{DC}
Total Capacitance (Maximum)	Ст	-100 V @ 100 MHz	0.8 pF
Series Resistance (Maximum)	R _S	+100 mA @ 100 MHz	0.5 Ohms
Parallel Resistance (Minimum)	R _P	-10 V @ 100 MHz	75 K Ω
Carrier Lifetime (Nominal)	τι	+6 mA / -10 mA @ (50% - 90% Voltage)	4.5 <i>u</i> s
I-Region Length (Nominal)	μ m	-	100 μm
C.W. Thermal Resistance (Maximum)	θ	-	20 °C/W
Power Dissipation in Free Air (Maximum)	W	I _F = +100 mA	2.5 W
Power Dissipation (Maximum)	P _D	I _F = +100 mA	7.5 W

Environmental Capability


MELF devices are appropriate for use in industrial and military applications and can be screened to meet the environmental requirements of MIL-STD-750, MIL-STD-202 as well as other military standards. The table below lists some of the MIL-STD 750 tests the device is designed to meet.


Test	Method	Description
High Temperature Storage	1031	+150°C, for 340 Hours
Temperature Shock	1051	-65°C to +150°C, 20 Cycles
HTRB	1038	80% of rated V _B , +150°C, for 96 Hours
Moisture Resistance	1021	No Initial Conditioning, 85% RH, +85°C
Gross Leak	1071 Cond. E	Dye Penetrant Visual
Vibration Fatigue	2046	20,000G's, 60Hz, x, y, z axis
Solderability	2026	Test Temperature = +245°C



Rev. V3

Typical Electrical Performance @ +25°C









Rev. V3

Typical Electrical Performance @ +25°C








Rev. V3

Typical Non-Magnetic Performance



Typical Magnetic Properties of Non-Magnetic MA4P7464F-1072T Device vs. Conventional MA4P1250-1072T Magnetic Device


Magnetic Property	MA4P7464F-1072T Value	MA4P1250-1072T Value
Saturation Moment (EMU) @ H = H _{MAX} Oersteads	2.3 x E-4	2.1 x E-2
Remanance Moment (EMU) @ H = 0 Oersteads	4.2 x E-8	7.1 x E-3
Coercivity (Oersteads) @ EMU = 0 Moment	1	59.2




Rev. V3

Mechanical Outline

1072 MELF Surface Mount Package



Circuit Pad Layout for 1072 MELF



Dimension	INCHES		ММ	
	MIN.	MAX.	MIN.	MAX.
Α	0.080	0.095	2.032	2.413
В	0.115	0.135	2.921	3.429
С	0.008	0.030	0.203	0.762
1072 Package (tape and reel only) 1500pcs/reel				

Dimension	Package Style 1072	
	inches	mm
А	0.093	2.36
В	0.050	1.27
С	0.060	1.52

Ordering Information

Part Number	Package	Quantity per Reel
MA4P7464F-1072T	Tape and Reel	1500pcs

MA4P7464F-1072T



Non Magnetic SMQ MELF PIN Diode

Rev. V3

M/A-COM Technology Solutions Inc. All rights reserved.

Information in this document is provided in connection with M/A-COM Technology Solutions Inc ("MACOM") products. These materials are provided by MACOM as a service to its customers and may be used for informational purposes only. Except as provided in MACOM's Terms and Conditions of Sale for such products or in any separate agreement related to this document, MACOM assumes no liability whatsoever. MACOM assumes no responsibility for errors or omissions in these materials. MACOM may make changes to specifications and product descriptions at any time, without notice. MACOM makes no commitment to update the information and shall have no responsibility whatsoever for conflicts or incompatibilities arising from future changes to its specifications and product descriptions. No license, express or implied, by estoppels or otherwise, to any intellectual property rights is granted by this document.

THESE MATERIALS ARE PROVIDED "AS IS" WITHOUT WARRANTY OF ANY KIND, EITHER EXPRESS OR IMPLIED, RELATING TO SALE AND/OR USE OF MACOM PRODUCTS INCLUDING LIABILITY OR WARRANTIES RELATING TO FITNESS FOR A PARTICULAR PURPOSE, CONSEQUENTIAL OR INCIDENTAL DAMAGES, MERCHANTABILITY, OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT. MACOM FURTHER DOES NOT WARRANT THE ACCURACY OR COMPLETENESS OF THE INFORMATION, TEXT, GRAPHICS OR OTHER ITEMS CONTAINED WITHIN THESE MATERIALS. MACOM SHALL NOT BE LIABLE FOR ANY SPECIAL, INDIRECT, INCIDENTAL, OR CONSEQUENTIAL DAMAGES, INCLUDING WITHOUT LIMITATION, LOST REVENUES OR LOST PROFITS, WHICH MAY RESULT FROM THE USE OF THESE MATERIALS.

MACOM products are not intended for use in medical, lifesaving or life sustaining applications. MACOM customers using or selling MACOM products for use in such applications do so at their own risk and agree to fully indemnify MACOM for any damages resulting from such improper use or sale.