






STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR CABLE .141

PAGE <b>1/3</b>	ISSUE <b>20-11-17B</b>	SERIES <b>4.3-10</b>	PART NUMBER <b>R183052007</b>
-----------------	------------------------	----------------------	-------------------------------







All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body	BRASS	BBR	
•			
Center contact	BRASS	SILVER	
Outer contact			
Insulator	PTFE		
Gasket	EPDM		
Others parts	BRASS	BBR	
Retaining ring	STAINLESS STEEL	-	
-	-	-	



## **Technical Data Sheet**

STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR CABLE .141

PAGE <b>2/3</b>	ISSUE <b>20-11-17B</b>	SERIES <b>4.3-10</b>	PART NUMBER <b>R183052007</b>
-----------------	------------------------	----------------------	-------------------------------

#### **PACKAGING**

Standard	Unit	Other
50	Contact us	Contact us

#### **ELECTRICAL CHARACTERISTICS**

Impedance 50 Ω Frequency 0-6 GHz **VSWR** 1.02 0.0100 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.05 RF leakage NA - F(GHz)) dB Maxi - ( Voltage rating 335 Veff Maxi Dielectric withstanding voltage 1000 Veff mini Insulation resistance 5000  $M\Omega$  mini

#### **MECHANICAL CHARACTERISTICS**

Center contact retention

Recommended torque

 Mating
 NA
 N.cm

 Panel nut
 NA
 N.cm

 Clamp nut
 NA
 N.cm

 A/F clamp nut
 0.0000
 mm

Mating life 100 Cycles mini

Weight **28.7280** g

#### **ENVIRONMENTAL**

Operating temperature -55/+90 °C
Hermetic seal NA Atm.cm3/s
Panel leakage NA

**SPECIFICATION** 

### **CABLE ASSEMBLY**

Stripping	а	b	С	d	е	f
mm	4.8	0	0	0	0	0

Assembly instruction: Solder 02

Recommended cable(s)

RG 402 KS 2

BELDEN 1673A HC80000-3 SUCOFORM 141

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly.

Cable retention

# **TOOLING**

Part Number	Description	Hexagon
R282744325	SOLDERING POSITIONER	

# OTHER CHARACTERISTICS

IP67 mated condition PIM3<=-123dBm, 2 carriers of +43dBm





STRAIGHT PUSH PULL PLUG SOLDER TYPE FOR CABLE .141

PAGE **3/3** ISSUE **20-11-17B SERIES 4.3-10** PART NUMBER R183052007 COMPONENT INSULATOR CENTER CONTACT BODY 3 Strip the dielectric of the cable. Screw the positioner onto the soldering jig. Clean the cable. Slide the cable assembly until it bottoms against positioner. Tighten and solder the contact. SOLDER TIGHTEN CABLE SOLDERING JIG POSITIONER CONTACT **INSULATOR** 2 4 Slide the insulator and the center contact onto the cable inner conductor CABLE IN POSITION SOLDER TIGHTEN Insulator SOLDERING JIG POSITIONER