




STRAIGHT JACK RECEPTACLE FOR PCB NON MAGNETIC SOLDER LEGS





# **Technical Data Sheet**

STRAIGHT JACK RECEPTACLE FOR PCB NON MAGNETIC SOLDER LEGS

PAGE <b>2/2</b>	ISSUE <b>30-06-15A</b>	SERIES MCX	PART NUMBER <b>R113426097</b>
-----------------	------------------------	------------	-------------------------------

#### **PACKAGING**

Standard	Unit	Other
100	Contact us	Contact us

## **ELECTRICAL CHARACTERISTICS**

Ω

Impedance 50 Frequency 0-6 GHz **VSWR** \*\*1.05 0.0300 x F(GHz) Maxi Insertion loss \*0.05 √F(GHz) dB Maxi - F(GHz)) dB Maxi RF leakage NA - ( Voltage rating 335 Veff Maxi Dielectric withstanding voltage 1000 Veff mini Insulation resistance 1000  $M\Omega$  mini

#### **MECHANICAL CHARACTERISTICS**

Center contact retention

Axial force – Mating End Axial force – Opposite end 10 N mini N mini 10 Torque NA N.cm mini

Recommended torque

Mating NA N.cm Panel nut NA N.cm

Mating life 500 Cycles mini Weight 0.7230

## **ENVIRONMENTAL**

-55/+125 °С Operating temperature Hermetic seal NA Atm.cm3/s Panel leakage NA

# **SPECIFICATION**

#### **OTHER CHARACTERISTICS**

Assembly instruction: NA

# Others:

- \* Coaxial Transmission Line Only
- \*\* Performance strongly depends on lay out and pcb material Distortion of the magnetic field : <= 0.5 ppm@ 10 mm @ Bo = 1.5 Tesla