
	\subset
	Ι,
M	U
	Ι,
	<u> </u>
	<u>`</u>
	\bigcup
	\cup
1	



NOTES:

MATERIALS:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B". 2. ALL METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACTS = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 01/11/17 DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior a RADIALL company written permission of RADIALL.						
DECIMAL	ANGLE	N.D. APVD: J.M.	01/11/17 DATE 01/11/17	SMC RIGHT ANGLE MALE JACK P.C.B. MOUNT						
REFERENCE: ORIGINATED: D.N. DATE: 01/11/17		MATERIALS & FINISHES: SEE NOTES		size A	FSCM NO. 19505	DWG NO. 1010-15	511	-001	rev A	
				SCALE	5:1	THIRD ANGLE PROJECTION	=	SHEET 1 O	F 1	