






N FEMALE COAXIAL TERMINATION 18GHZ 1W

PAGE 1/2 ISSUE 24-02-15A SERIES PART NUMBER R404355150





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Center contact Outer contact Insulator Gasket Substrate	STAINLESS STEEL BERYLLIUM COPPER - PTFE - ALUMINA CERAMIC	PASSIVATED GOLD OVER NICKEL -
Resistor Others parts	THIN FILM -	-





N FEMALE COAXIAL TERMINATION 18GHZ 1W

PAGE 2/2	ISSUE 24-02-15A	SERIES TERMINATION	PART NUMBER R404355150
-----------------	------------------------	-----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Operating Frequency Range	DC-18	GHz
Impedance	50	Ω
DC Resistance	50	Ω ± 5%
Peak power at 25°C (1µs, 1‰)	50	W
verage power at 25°C 1 W (Free Air Cool		W (Free Air Cooled)
		W (Conduction Cooled)
'		· · · · · · · · · · · · · · · · · · ·


MECHANICAL CHARACTERISTICS

Connectors	N	Female	MIL C 39012
Weight	41,3600 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS