



# ALUMINUM ELECTROLYTIC CAPACITORS

# LGC

Snap-in Terminal Type,  
105°C Long Life Assurance, Ultra-Smaller-Sized




- One rank smaller case sized than LGX.
- Suited for equipment down sizing.
- Compliant of the RoHS directive (2011/65/EU,(EU)2015/863).



## Specifications


Item	Performance Characteristics	
Category Temperature Range	- 40 to +105°C	
Rated Voltage Range	500V	
Rated Capacitance Range	68 to 680μF	
Capacitance Tolerance	±20% at 120Hz, 20°C	
Leakage Current	$I \leq 3\sqrt{CV}$ (μA) (After 5 minutes' application of rated voltage at 20°C) [C : Rated Capacitance (μF) V : Voltage (V)]	
Tangent of loss angle (tan δ)	0.25max. 120Hz at 20°C	
Stability at Low Temperature	Impedance ratio $Z(-25^\circ\text{C}) / Z(+20^\circ\text{C}) \leq 8$ (120Hz)	
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 5000 hours at 105°C, the peak voltage shall not exceed the rated voltage.	
	Capacitance change	Within ±20% of the initial capacitance value
	tan δ	200% or less than the initial specified value
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the requirements listed at right.	
	Capacitance change	Within ±15% of the initial capacitance value
	tan δ	150% or less than the initial specified value
Leakage current	Less than or equal to the initial specified value	
	Leakage current	Less than or equal to the initial specified value
Marking	Printed with white color letter on black sleeve.	

## Drawing



※ Other terminations available upon request.  
Please refer to the Guidelines for Aluminum Electrolytic Capacitors.

## Type numbering system (Example : 500V 100μF)



## Dimensions

500V (2H)				
Cap. (μF)	Size φD × L(mm)	Rated ripple (mArms)	Leakage Current (mA)	Code
68	22 × 25	690	0.55	LGC2H680MELZ25
100	22 × 30	850	0.67	LGC2H101MELZ30
120	22 × 35	960	0.73	LGC2H121MELZ35
150	22 × 40	1110	0.82	LGC2H151MELZ40
	25 × 30	1060	0.82	LGC2H151MELA30
180	22 × 45	1250	0.90	LGC2H181MELZ45
	25 × 35	1200	0.90	LGC2H181MELA35
220	22 × 50	1400	0.99	LGC2H221MELZ50
	25 × 40	1360	0.99	LGC2H221MELA40
	30 × 30	1290	0.99	LGC2H221MELB30
	35 × 25	1200	0.99	LGC2H221MELC25
270	22 × 60	1620	1.10	LGC2H271MELZ60
	25 × 50	1600	1.10	LGC2H271MELA50
	30 × 35	1480	1.10	LGC2H271MELB35
	35 × 30	1430	1.10	LGC2H271MELC30
330	25 × 55	1780	1.21	LGC2H331MELA55
	30 × 40	1670	1.21	LGC2H331MELB40
	35 × 35	1630	1.21	LGC2H331MELC35
390	30 × 45	1850	1.32	LGC2H391MELB45
	35 × 40	1820	1.32	LGC2H391MELC40
470	30 × 55	2140	1.45	LGC2H471MELB55
	35 × 45	2020	1.45	LGC2H471MELC45
560	30 × 60	2340	1.58	LGC2H561MELB60
	35 × 50	2230	1.58	LGC2H561MELC50
680	35 × 55	2440	1.74	LGC2H681MELC55

Rated ripple current (mArms) at 105°C 120Hz

CAT.8100M

## Frequency coefficient of rated ripple current

Frequency (Hz)	50	60	120	300	1 k	10k	50k or more
Coefficient	0.77	0.82	1.00	1.16	1.30	1.41	1.43