



Electrical specifications

Center Frequency: 707 MHz
Bandwidth: 18 MHz
VSWR in BW: 12 dB min.
Input / Output Impedance: 50 Ohms
Passband: 698-716 MHz
Passband Insertion Loss: 3.0 dB max.
Passband Ripple: 0.5 dB max.
Rejection: 40dB min. @ 628-646 MHz
Rejection 2: 40 dB min. @ 558-576 MHz
Rejection 3: 30 dB min. @ 768-786 MHz
Power Handling: 1 W

Mechanical




Mounting Method: SMT
Dimensions: 13 x 12 x 36 mm max

Environmental

Operating Temperature: -20°C to 85°C
Storage Temperature: -50°C to +90°C

This product is RoHs compliant.

Outline Drawing:



■ : I/O PORT
 ▨ : GROUND

TOLERANCE UNLESS OTHERWISE SPECIFIED : ±0.2
DIMENSIONS : mm