





EMBASE A ECROU A MONTAGE AVANT PACKAGING 100

PAGE 1/2 ISSUE 15-01-15B SERIES BR2 PART NUMBER R605550020





All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	NICKEL
Center contact	BERYLLIUM COPPER	GOLD OVER NICKEL
Outer contact	-	-
Insulator	POLYAMIDES 11	
Gasket	-	
Others parts	-	-
-	-	-
-	-	-



Technical Data Sheet

EMBASE A ECROU A MONTAGE AVANT PACKAGING 100

PAGE 2/2 ISSUE 15-01-15B SERIES BR2	PART NUMBER R605550020
-------------------------------------	-------------------------------

PACKAGING

Standard	Unit	Other
100	Contact us	Contact us

ELECTRICAL CHARACTERISTICS

 $\begin{array}{ccc} \text{Impedance} & \textbf{80} & \Omega \\ \text{Frequency} & \textbf{0-0.5} & \text{GHz} \end{array}$

x F(GHz) Maxi √F(GHz) dB Maxi 0,0000 VSWR Insertion loss NA - F(GHz)) dB Maxi RF leakage NA - (Voltage rating 500 Veff Maxi Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End

Axial force - Opposite end

Torque

27 N mini
27 N mini
27 N mini
27 N.cm mini

Recommended torque

 Mating
 - N.cm

 Panel nut
 250 N.cm

Mating life 500 Cycles mini Weight 0,0000 g

ENVIRONMENTAL

Operating temperature -40/+100 °C Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

OTHER CHARACTERISTICS

Assembly instruction:

Others:

-