



3015.625 MHz Ceramic Bandpass Filter

ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

Part Number: AM3015B1482



Electrical specifications

Center Frequency: 3015.625 MHz
Bandwidth: 31.25 MHz min
VSWR: 1.5 : 1 max
Input / Output Impedance: 50 Ohms
Passband: 3000-3031.25 MHz
Passband Insertion Loss: 5.0 dB max
Passband Ripple: 1.0 dB max
Rejection: 30 dB min @ 2831.25-2862.5 MHz
Rejection 2: 28 dB min @ 2931.25 MHz
Rejection 3: 28 dB min @ 3080-6000 MHz
Power Handling: 23 dBm max

Mechanical


Mounting Method: SMT
Dimensions: 13 x 12 x 5.5mm

Environmental

Operating Temperature: -40°C to 85°C
Storage Temperature: -50°C to +90°C

This product is RoHs compliant.

Outline Drawing:



UNIT:mm
TOLERANCE:±0.3

Available at our Web store:



70 Outwater Lane Phone: (973) 772-4242
Garfield, NJ 07026 Fax : (973) 772-4646

Email: sales@anatechelectronics.com
Web: www.anatechelectronics.com