



Product: FS1BNC-25

ProSNS Mini BNC Coax Compression Connector 24-26 AWG

Product Description

ProSNS Mini (24-26 AWG) BNC connector for coaxial cable. Non-blind entry with split ferrule design, polymer compression sleeve for easy insertion & lowest possible tool compression force. 25 per Pack

Technical Specifications

Product Overview

Suitable Applications:	CCTV, Security Cameras, Video
Physical Characteristics	; (Overall)
Packaging:	25 Pack
Number of Pieces:	1
Connectors	
Materials	
Material	
Nickel/Tin Plated Brass	
Nickel/Tin Plated Brass	
Gold Plated	
Nominal Characteristic Impeda	
Return Loss (RL)	
Frequency [MHz]	
DC-1 GHz 23 dB Return Loss 1.	I6 VSWR
DC-2 GHz 20 dB Return Loss 1.2	20 VSWR
DC-3 GHz 20 dB Return Loss 1.2	20 VSWR
Mechanical Characteris	tics
Footprint/Type:	Соах
Connector Interface Type:	BNC
Gender:	Male - plug
Connector Series Name:	ProSNS

Connector Series Name:	ProSNS
Color Band:	Orange
Locking:	No
Tool Compatibility:	CPLCCT-SLMR (compression), PSA59/6/RGB (strip)
Termination Type:	Compression
Cable Center Conductor Diameter Limits:	.015025 inch
Cable Dielectric Diameter Limits:	.065078 inch
Cable Outer Jacket Diameter Limits:	.095110 inch

Applicable Environmental and Other Programs

	<u> </u>
EU CE Mark:	Yes
Related Part Numbers	
Variants	
Item # Color UPC	
FS1BNC-25 No Color 845671000139	
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents-
History	
Update and Revision:	Revision Number: 0.111 Revision Date: 03-04-2023

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.