
	REVISIONS				
	REV.	DESCRIPTION	DATE	APPROVED	
Ì	А	INITIAL RELEASE	02/06/14	J.S.	



NOTES:

MATERIALS:

- LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 INSULATOR = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.
 ALL OTHER METAL PARTS = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 0, GRADE C, OVER .00010 TO .00020 COPPER STRIKE PER MIL-C-14550.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: DATE J.S. 02/06/1 CHKD: DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior RADIALL companywritten permission of RADIALL.		
DECIMAL ANGLE D.		D.N. 02/06/1	750HM STRAIGHT MALE JACK		
		APVD: DATE	SCREW ON REAR MOUNT		
		J.M. 02/06/1	BULKHEAD RECEPTACLE		
REFERENCE:		MATERIALS & FINISHES:	SIZE FSCM NO. DWG NO.	REV	
ORIGINATED: J.S.		SEE NOTES	A 19505 1704-1511-000	I A	
DATE: 02/06/14			SCALE 6:1 THIRD ANGLE SHEET 1 C	OF 1	