
	PANEL THICKNESS AND HARDWARE INSTALLATION															,			
	12BW07 - LARGE SHOULDER NUT (K620)										12BW11 - SMALL SHOULDER NUT (K619)								
PANEL THICKNESS	0.050	0.055	0.060	0.065	0.070	0.075	0.080	0.085	0.090	0.095	0.100	0.105	0.110	0.115	0.120	0.125			
WASHER (K178)	YES	YES	YES	YES	YES	NO	NO	NO	NO	YES	YES	YES	YES	YES	NO	NO			




SEALED JACK (WHEN MATED)




- 1. INSTALLATION SEE THE PANEL THICKNESS AND HARDWARE INSTALLATION TABLE. INSTALL THE JACK AND THE WASHER (IF NEEDED) FROM THE BACK OF THE PANEL. INSTALL THE O-RING AND THEN THE SHOULDER NUT FROM THE FRONT OF THE PANEL. TIGHTEN THE NUT.
- 2. TO BE USED WITH SWITCHCRAFT 267S15-S28 SERIES PLUGS FOR IP66 RATING WHEN MATED.
- 3. RECOMMENDED MOUNTING HOLE:  $\emptyset$  0.375 [9.5]
- 4. RECOMMENDED WORKING TEMPERATURE: -20 TO 50 °C.
- 5. MATERIALS:

BUSHING - BRASS, NICKEL PLATED
INSULATING WASHERS, PHENOLIC
SLEEVE TERMINAL - BRASS, HOT TIN COATED
TIP & RING SPRING - NICKEL SILVER
O-RING - RUBBER
METAL WASHERS - STEEL, NICKEL PLATED
SHOULDER NUT - BRASS, NICKEL PLATED

6. THIS PRODUCT IS ROHS COMPLIANT.





## **CUSTOMER DRAWING**

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.  SIZE WIDTH MULT LBS/M TEMPER  1. ALL DIMENSIONS IN INCHES [mm]  - TWO PLACE DECIMALS ±0.02 [0.5]  - THREE PLACE DECIMALS ±0.005 [0.13]  THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.  SIZE WIDTH MULT LBS/M TEMPER  FINISH  SPEC No.  FIRST USED ON SCALE  2:1  DATE DRAWN BY CHKD APVD  DATE DRAWN BY CHKD APVD  DATE DRAWN BY CHKD APVD  SPEC NO.  SPEC NO.  FIRST USED ON SCALE  2:1		_					·										
1. ALL DIMENSIONS IN INCHES [mm]  - TWO PLACE DECIMALS ±0.02 [0.5]  - THREE PLACE DECIMALS ±0.005 [0.13]																	
- TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]  SPEC No.  FIRST USED ON SCALE 2:1  DATE DRAWN BY CHKD APVD							UNLESS OTHERWISE SPECIFIED	SIZE	V	/IDTH	ΓH MULT		LBS/M	M TEM		PER	
- THREE PLACE DECIMALS ±0.005 [0.13]  FIRST USED ON SCALE 2:1  DATE DRAWN BY CHKD APVD							1. ALL DIMENSIONS IN INCHES [mm]	FINISH				MATERIAL					
- THREE PLACE DECIMALS ±0.005 [0.13] FIRST USED ON SCALE 2:1  DATE DRAWN BY CHKD APVD							- TWO PLACE DECIMALS +0.02 [0.5]	SPEC No.				SPEC No.					
								FIRST USED ON								<u></u>	®
								DATE DRAWN	BY	CHKD	APVD						
								2/17/20	NIS	NS	SRC						
A 28492 5/18/22 TJK TJK	A	28492	5/18/22	8/22   T	JK T	JK		2/1//20	NO	2/17/20	2/17/20		SHEET	1	OF	1	
INLY LOO NOMBER DATE BY ALVO	REV	ECO NUMBER	DATE	TE B	BY AF	VD _											REV
REVISIONS DO NOT SCALE DRAWING SEALED 1/4" STEREO JACK, RoHS 12BW07-W11 A	REVISIONS				<b>'</b>		DO NOT SCALE DRAWING	SEALED 1/	12BW07-W11 A					Α			