

BODY:

STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1; OR ASTM A582 TYPE 303, COND. A

BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04 CONTACT:

INSULATORS: PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS

FINISH:

BODY: PASSIVATED PER AMS-2700

CONTACT:

GOLD PER ASTM B488, TYPE II, CODE C, CLASS 0.76, OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .00005" MIN.

PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 26.5 GHz.

NOTES:

- 1. FOR DROP IN REPLACEMENT WITH HIGHER PERFORMANCE SEE SV SF2921-61560.
- 2. FOR A FOOTPRINT RECOMMENDATION SPECIFIC TO YOUR PCB, PLEASE CONTACT US AT applications@svmicro.com

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: +1/64 ANGULAR: X° +1°0′	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS] 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS.		MICROWAVE www.svmicrowave.com			
FINISH:	SEE NOTES	DECIMAL: .X ±.030 .XX ±.010						
SURFACE AREA: N/A		.XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES	5) SURFACE ROUGHNESS 63	CE ROUGHNESS 63. MIL-STD-10. N COMMON CENTERS TO BE CONCENTRIC .005 T.I.R.		SMA FEMALE SOLDERLESS		
	PROPRIETARY	PER ASME Y14.5M - 1994	T) NEWOVE ALE BOING		EDGE LAUNCH CONNECTOR			
	ATION CONTAINED IN THIS DRAWING	THIRD ANGLE PROJECTION	DRAWN:	JPM 05/19/21	_	LACINOTI CONNL	-0101	
ANY REPRODI	E PROPERTY OF SV MICROWAVE, INC. DUCTION IN PART OR AS A WHOLE HE WRITTEN PERMISSION OF		CHECKED:	SEE PDM	SIZE DWG. NO.	2921-6	61674	
	VE, INC IS PROHIBITED.		APPROVED:	SFF PDM	SCALE: 10:1		SHEET 1 OF 1	