
# Pomona®

## Model Models 1325, 5230 & 5406 Do-It-Yourself Banana Plug, Solderless Stackable Type For Standard Banana Jacks



#### **FEATURES:**

- Designed to fit on the end of any 22 AWG to 18 AWG wire.
- Cross hole wire entry fits wires up to .12" (3mm) diameter
- Set screw clamps wire firmly with flat blade screwdriver
- Available with tarnish resistant nickel or gold plating for very low contact resistance
- Model 5230 is compatible to high temperatures up to +150°C (+302°F)
- Set screw simplifies assembly of test leads and jumpers
- Fits standard panel and binding post banana jacks .161" to .166" (4,0mm to 4,2mm) diameter

### **RATINGS:**

Operating Voltage: Hand-held Testing: 30VAC/60VDC Max.

Hand Free Testing in controlled Voltage Environment: 5000 WVDC.

Operating Temperature: +50°C (+122°F) Max. Model 5230: +150°C (+302°F)

Current: 15 Amperes

#### ORDERING INFORMATION:

Model 1325-0 Nickel Plated Banana Plug with Black Insulation

Model 1325-1 Nickel Plated Banana Plug with Brown Insulation

Model 1325-2 Nickel Plated Banana Plug with Red Insulation

Model 1325-3 Nickel Plated Banana Plug with Orange Insulation

Model 1325-4 Nickel Plated Banana Plug with Yellow Insulation

Model 1325-5 Nickel Plated Banana Plug with Green Insulation

Model 1325-6 Nickel Plated Banana Plug with Blue Insulation

Model 1325-7 Nickel Plated Banana Plug with Violet Insulation

Model 1325-8 Nickel Plated Banana Plug with Gray Insulation

Model 1325-9 Nickel Plated Banana Plug with White Insulation

Model 5406-0 Gold Plated Banana Plug with Black Insulation

Model 5406-2 Gold Plated Banana Plug with Red Insulation

Model **5230-0** Nickel Plated Banana High Temperature Plug with Black Insulation

Model 5230-6 Nickel Plated Banana High Temperature Plug with Blue Insulation

All dimensions are in inches. Tolerances (except noted):  $.xx = \pm .02$ " (,51 mm),  $.xxx = \pm .005$ " (,127 mm). All specifications are to the latest revisions. Specifications are subject to change without notice. Registered trademarks are the property of their respective companies. Made in USA

