






STRAIGHT PLUG CRIMP TYPE CABLE 6.1/50D

PAGE 1/3 ISSUE 15-05-15B SERIES QMA PART NUMBER R123076310







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	BRASS	BBR
Center contact	BRASS	NPGR
Outer contact	BRONZE	BBR
Insulator	PTFE	
Gasket	-	
Others parts	BRASS	BBR
-	-	-
-	-	-



# **Technical Data Sheet**

STRAIGHT PLUG CRIMP TYPE CABLE 6.1/50D

PAGE **2/3** ISSUE 15-05-15B SERIES QMA PART NUMBER R123076310

#### **PACKAGING**

Standard	Unit	Other
100	Contact us	Contact us

#### **ELECTRICAL CHARACTERISTICS**

50 Impedance Frequency 0-6 GHz **VSWR** 1.12\* 0.0000 x F(GHz) Maxi Insertion loss 0.05 √F(GHz) dB Maxi RF leakage \*\*80 - F(GHz)) dB Maxi - ( Voltage rating Veff Maxi 335 Dielectric withstanding voltage 1000 Veff mini Insulation resistance 5000  $M\Omega$  mini

### **MECHANICAL CHARACTERISTICS**

Center contact retention

Axial force - Mating End 18 N mini Axial force - Opposite end 18 N mini Torque NA N.cm mini

Recommended torque

Mating NA N.cm Panel nut NA N.cm Clamp nut NA N.cm A/F clamp nut 0.0000 mm

Mating life 100 Cycles mini 7.3700 g

Weight

#### **ENVIRONMENTAL**

Operating temperature -40/+105 °C Hermetic seal NA Atm.cm3/s Panel leakage NA

#### **SPECIFICATION**

### **CABLE ASSEMBLY**

Stripping	а	b	С	d	е	f
mm	4.2	10	15	0	10.8	0

Assembly instruction: SEE PAGE 3

Recommended cable(s)

**KSR240 LMR 240** 

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

- pull off 220 N mini - torque N.cm

# **TOOLING**

Part Number	Description	Hexagon
R282223000	CRIMPING TOOL	
R282235013	CRIMPING DIES	
R282293000	CRIMPING TOOL M22520/5-01	

# OTHER CHARACTERISTICS

\*VSWR: 1.12 max@0-3GHz, 1.2 max@3-6GHz \*\*RF: leakage(interf.): 3<F<6GHz: <-70dB





STRAIGHT PLUG CRIMP TYPE CABLE 6.1/50D

PAGE **3/3** ISSUE 15-05-15B SERIES QMA PART NUMBER R123076310 COMPONENTS STRIPPING DIMENSIONS Centre contact b Body Ferrule Insulator 4 Slide the ferrule onto the cable. Slide cable into body until it bottoms against insulator. Strip the cable. 2 5 Fan the braid. Slide the ferrule over the braid. Slide the insulator on the cable centre contact until it bottoms against the cable dielectric. Slide on the centre contact until it bottoms against the Crimp the ferrule with crimping tool ( see connector TDS ). additional insulator. Cut the excess of braid if necessary. Solder the centre contact with crimping tool. Clean solder area if necessary. 2