TCO Series

Conductive Polymer Chip Capacitors (Standard)





FEATURES

- · Ta-polymer technology
- High ripple capability
- Surge robust
- J-lead LF


APPLICATIONS

- DC/DC
- Industrial
- Computers
- Telecom
- IoT
- Home applications





MARKING




CASE DIMENSIONS:

millimeters (inches)

	Code	EIA Code	EIA Metric	L±0.20 (0.008)	W±0.20 (0.008)	H±0.20 (0.008)	W ₁ ±0.20 (0.008)	A±0.30 (0.012)
[В	1210	3528-21	3.50 (0.138)	2.80 (0.110)	1.90 (0.075)	1.90 (0.075)	0.80 (0.031)

HOW TO ORDER





Capacitance Code pF code: 1st two digits represent significant figures, 3rd digit represents multiplier (number of zeros to follow)

336

М **Tolerance** $M = \pm 20\%$

8R **Packaging** 8 = Tape width R = Positive electrode on the side opposite to

sprocket hole



Discrimination code

TECHNICAL SPECIFICATIONS

Technical Data:	All technical data relate to an ambient temperature of +25°C	
Capacitance Range:	15μF to 330μF	
Capacitance Tolerance:	±20%	
Leakage Current DCL:	Please see the ratings and part number reference table below	
Temperature Range:	-55°C to +105°C	

Note: Conductive Polymer Capacitors are designed to operate within the limits of the environmental conditions specified for each series. If operated continuously at their maximum temperature and / or humidity limit, or beyond these limits, capacitors may exhibit a parametric shift in capacitance and increases in ESR. These changes may occur earlier if the specified environmental conditions are exceeded. Similarly, their normal operational time period will be significantly extended if their general duty cycle includes operation below maximum temperature within humidity controlled environments. Careful attention should be paid to maximum temperature with associated high humidity environments as well as voltage derating, ripple current and current surges.

Please reference the KYOCERA AVX Conductive Polymer Capacitor Guidelines for more information or contact factory for application assistance



TCO Series





CAPACITANCE AND RATED VOLTAGE RANGE (LETTER DENOTES CASE SIZE)

Capac	itance	Rated Voltage DC (V _R) @ 105°C							
μF	Code	2.5V(e)	6.3V(j)	10V(A)	16V(C)	25V(E)	Code		
15	156					100	е		
22	226					90	j		
33	336			150	100		n		
47	476			150			S		
100	107		35,45				ā		
150	157		35,45				ē		
220	227	35	35				Ĭ		
330	337	35,45					ñ		

Released ratings, (ESR ratings in mOhms)

Note: Voltage ratings are minimum values. KYOCERA AVX reserves the right to supply higher volage ratings in the same case size, to the same reliability standards.

RATINGS & PART NUMBER REFERENCE

Part No.	Case Size	Capacitance (µF)	Rated Voltage (V)	Maximum Operating Temp. (°C)	DCL Max. (μA)	DF Max. (%)	ESR Max. @100kHz (mΩ)	100kHz RMS Current (mA) 45°C	MSL	
2.5 Volt										
TCOB0E227M8R-EN1	В	220	2.5	105	55.0	8	35	1900	3	
TCOB0E337M8R-EN2	В	330	2.5	105	82.5	15	35	1900	3	
TCOB0E337M8R-ES2	В	330	2.5	105	82.5	15	45	1700	3	
	6.3 Volt									
TCOB0J107M8R-EN1	В	100	6.3	105	63.0	8	35	1900	3	
TCOB0J107M8R-ES1	В	100	6.3	105	63.0	8	45	1700	3	
TCOB0J157M8R-EN1	В	150	6.3	105	95.5	15	35	1900	3	
TCOB0J157M8R-ES2	В	150	6.3	105	94.5	15	45	1700	3	
TCOB0J227M8R-EN1	В	220	6.3	105	139.0	15	35	1900	3	
				10 Volt						
TCOB1A336M8R	В	33	10	105	33.0	8	150	900	3	
TCOB1A476M8R	В	47	10	105	47.0	8	150	900	3	
				16 Volt						
TCOB1C336M8R	В	33	16	105	159.0	10	100	1100	3	
				25 Volt						
TCOB1E156M8R	В	15	25	105	113.0	10	100	1100	3	
TCOB1E226M8R-EB1	В	22	25	105	55.0	10	90	1200	3	

Moisture Sensitivity Level (MSL) is defined according to J-STD-020.

All technical data relates to an ambient temperature of +25C.

Capacitance and DF are measured at 120Hz, 0.5RMS with DC bias of 1.5 volts.

DCL is measured at rated voltage after 5 minutes.

ESR allowed to move up to 1.25 times catalog limit post mounting.

NOTE: KYOCERA AVX reserves the rights to supply higher voltage rating in the same case size, to the same reliability standards.

TCO Series






QUALIFICATION TABLE

TECT	TCO series (Temperature range -55°C to +105°C)								
TEST		Condition			Characteristics				
				Visual examination no visible damage					
		age (Ur) at 105°C fo		DCL	2x initial limit				
Endurance	_	resistence of ≤3.0Ω re for 24 hours befo		ΔC/C	within ±20% of initial value				
	100111 temperatu	16 101 24 110u13 beic	ore measuring.	DF	1.5x initial limit				
				Visual examination	no visible damage				
	1	90-95% relative hur	•	DCL	1.5x initial limit				
Humidity		oilize at room tempe nours before measu		ΔC/C	within +30/-20% of initial value				
	liumaity for 241	iours before mease	iiiig.	DF	1.5x initial limit				
	Step	Temperature°C	Duration(min)		-55°C	+105°C			
Temperature	2	-55 +105	15 15	DCL	n/a	10xIL*			
Stability		1103	10	ΔC/C	0/-20%	+80/0%			
				DF	IL*	IL*			
				Visual examination	no visible damage				
Surge Voltage		voltage (Ur) at 85± Sec charge and 30:		DCL	initial limit				
ourge voltage	resistance 1000		occ discridinge	ΔC/C	±20% of initial limit				
				DF	initial limit				
	4.17 JIS C 5101-	-1		Visual examination	no visible damage				
Vibration	Frequency: 10 to	55 to 10Hz/min.		DCL	initial limit				
Vibration	Amplitude: 1.5m	ım		ΔC/C	within ± 5% of initial value				
	Time: 2hours ea	ch in X and Y direct	ions	DF	initial limit				

For use outside of recommended conditions and special request, please contact KYOCERA AVX. Initial measurement max. 1hr after the removal from dry pack or after pretreatment at 85°C for 24 hours.

PACKAGING SPECIFICATIONS



Unit (mm)

Case	A±0.10	B±0.10	W±0.20	E±0.10	F±0.05	P1±0.10	P2±0.05	PO±0.10	DO+0.10/0	t1±0.05	t2±0.10	Standard packaging quantity
В	3.30	3.80	8.00	1.75	3.50	4.00	2.00	4.00	φ1.50	0.25	2.20	2,000 pcs

REEL DIMENSIONS

