






RIGHT ANGLE PLUG SOLDER TYPE CABLE 1/2" SUPER FLEXIBLE CORRUGATED

PAGE 1/3 ISSUE 08-06-15A SERIES 4.3-10 PART NUMBER R183165007







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body	BRASS	BBR	
•			
Center contact	BRASS	SILVER	
Outer contact	-	-	
Insulator	PTFE		
Gasket	EPDM, SILICONE RUBBER		
Others parts	BRASS	BBR	
-	-	-	
-	-	-	



Technical Data Sheet

RIGHT ANGLE PLUG SOLDER TYPE CABLE 1/2" SUPER FLEXIBLE CORRUGATED

PAGE 2/3 ISSUE 08-06-15A SERIES 4.3-10	PART NUMBER R183165007
--	-------------------------------

PACKAGING

50	Contact us	Contact us
Standard	Unit	Other

ELECTRICAL CHARACTERISTICS

Impedance			50	Ω
Frequency			0-6	GHz
VSWR	1.02	+	0.0200	x F(GHz) Maxi
Insertion loss			0.05	√F(GHz) dB Maxi
RF leakage	- (NA	- F(GHz)) dB Maxi
Voltage rating			1000	Veff Maxi
Dielectric withstanding voltage	ge		2500	Veff mini
Insulation resistance			5000	$M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention		
Axial force – Mating End	30	N mini
Axial force – Opposite end	30	N mini
Torque	NA	N.cm mini

Recommended torque

Mating 500 N.cm Panel nut NA N.cm Clamp nut NA N.cm A/F clamp nut 0.0000 mm

Mating life 100 Cycles mini Weight 49.8990 g

ENVIRONMENTAL

Operating temperature	-55~+90	°C
Hermetic seal	NA	Atm.cm3/s
Panel leakage	NA	

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	8.4	15	0	0	0	0

Assembly instruction:

Recommended cable(s)

FSJ4RN-50B HCF1/2"CuH-50oAlCu

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

assembly

350 - pull off N mini - torque 200 N.cm

TOOLING

Part Number	Description	Hexagon

OTHER CHARACTERISTICS

IP 67 mated condition PIM3<=-123dBm, 2 carriers of +43dBm







RIGHT ANGLE PLUG SOLDER TYPE CABLE 1/2" SUPER FLEXIBLE CORRUGATED

PAGE 3/3 ISSUE 08-06-15A SERIES 4.3-10 PART NUMBER R183165007

COMPONENTS


STRIPPING DIMENSIONS






1

- Strip the cable.
- Do not damage the outer conductor.
- The end surface of inner conductor should be chamfered
- Remove impurities such as copper scraps and burrs on the end surface of the cable.



2

- Wrap the cable by solder wire (Dia 1.2mm).



3

- Push the cable into the connector body, until it stops.
- Use the reserved solder wire to wrap the cable to fill the space between cable and connector.
- Solder the connector body with cable.
- Solder the inner conductor.
- Press the cap into body

