




## **ROHS COMPLIANT**











## Electrical Characteristics

Nominal Impedance: 50 ohms
Frequency Range: DC to 4 GHz
VSWR: 1.3:1 maximum
Insertion Loss: 0.2 dB at 3 GHz

Operating Voltage (rms): 500 V maximum at sea level
Dielectric Withstand Voltage (rms): 1500 V maximum at sea level
Contact Resistance: 3.0 milliohms maximum
Insulation Resistance: 5000 megohms minimum

## **Mechanical Characteristics**

Mating Cycles: 500 cycles minimum
Interface Dimensions: Conform to MIL-C-39012

## **Environmental Characteristics**

Temperature Range: -55 °C to +85 °C

REF.	DESCPIPTION	MATERIAL	PLATING	
1	Body	Zinc Alloy	Nickel	
2	Insulator	Polypropylene		
3	Ground Terminal	Copper-clad steel	Tin	
4	Socket Contact	Phosphor	Gold	
5	Mount Post	Brass	Tin >5 Microns	
6	Lock Washer	Brass	Nickel	
7	Hex Nut	Brass	Nickel	

	Complete Update	KA	4	13 Mar 08
	Updated for RoHS compliance	JW	3	30 Aug 06
	CAD Issue	SN	2	01 May 02
	First Issue	SN	1	15 March 00
ſ	DESCRIPTION OF REVISION	APPVD	ISS	DATE



Cinch Connectivity Solutions 7-13 Russel Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515

Fax: +44 (0) 1245 358938

SCALE: Not To Scale

DRAWN BY:

J Williams

DIMENSIONS: mm

CHECKED BY:

A Tusi

APPROVED BY:

A Herbert

DATE:

30 Aug 06

TITLE:

BNC Right Angle PCB Mount
Jack Low Profile

PART NUMBER:

**VBM211** 

PAGE: 1 of 1