

»Features

$V_{DS} = 20V$
 $I_D = 4A$
 $R_{DS(ON)} @ V_{GS} = 4.5V, TYP = 22m\Omega$
 $R_{DS(ON)} @ V_{GS} = 2.5V, TYP = 28m\Omega$

»General Description



- Very low on-resistance RDS(ON)
- High density cell design for ultra low Rdson
- Fully characterized avalanche voltage and current
- SOT23-6L for Surface Mount Package.

»APPLICATION

- Power switching application
- PWM applications
- Hard switched and high frequency circuits
- Uninterruptible power supply

»Absolute Maximum Ratings @ $T_A=25^\circ C$ unless otherwise noted

parameter	symbol	limit	unit
Drain-source voltage	V_{DS}	20	V
Gate-source voltage	V_{GS}	± 12	V
Continuous drain current ($T_J = 150^\circ C$) ^a	I_D	4.0	A
		3.0	
Pulsed drain current ^b	I_{DM}	20	
Continuous source current (diode conduction) ^a	I_S	1.2	
Power dissipation ^a	P_D	1.4	W
		0.9	
Operating junction and storage temperature range	T_J, T_{stg}	-55—150	°C

»Pin Configurations

SOT23-6L

»THERMAL CHARACTERISTICS

Parameter	Symbol	Typ	Max	Unit
Maximum junction-to-ambient ^a	≤ 10 s	$R_{\theta JA}$	70	90
	Steady-State		100	125
Maximum junction-to-foot	Steady-State	$R_{\theta JC}$	63	80

Notes

- a. Surface mounted on 1" x 1" FR4 board
- b. Pulse width limited by maximum junction temperature

»N-Channel Electrical Characteristics @ $T_A=25^\circ C$ unless otherwise noted


Parameter	Symbol	Condition	Min	Typ	Max	Unit
OFF Characteristics						
Drain-source breakdown voltage	BV_{DSS}	$V_{GS}=0V, I_D=250\mu A$	20	-	-	V
Zero gate voltage drain current	I_{DS}	$V_{DS}=20V, V_{GS}=0V$	-	-	1	μA
Gate-body leakage	I_{GSS}	$V_{DS}=0V, V_{GS}=\pm 12V$	-	-	± 100	nA
ON Characteristics						
Gate threshold voltage	$V_{GS(th)}$	$V_{DS}=V_{GS}, I_D=250\mu A$	0.5	0.75	1.2	V
Drain-source on-state resistance ^a	$R_{DS(ON)}$	$V_{GS}=4.5V, I_D=4.0A$	-	22	26	$m\Omega$
		$V_{GS}=2.5V, I_D=3.0A$		28	35	
Forward transconductance ^a	g_f	$V_{DS}=5V, I_D=4A$	-	10	-	S
Dynamic Characteristics ^b						
Input capacitance	C_{iss}	$V_{DS}=10V, V_{GS}=0V$ $f=1.0MHz$	-	600	-	pF
Output capacitance	C_{oss}		-	330	-	
Reverse transfer capacitance	C_{rss}		-	140	-	
Switching Characteristics						
Turn-on delay time	$t_{D(ON)}$	$V_{DD}=10V$ $R_L=3\text{ ohm}$ $V_{GEN}=4.5V$ $R_{GEN}=6\text{ohm}$	-	18	-	ns
Rise time	t_r		-	5	-	
Turn-off delay time	$t_{D(OFF)}$		-	43	-	
Fall time	t_f		-	20	-	
Total gate charge	Q_g	$V_{DS}=10V$ $I_D=4A$ $V_{GS}=4.5V$	-	11	-	nC
Gate-source charge	Q_{gs}		-	2.3	-	
Gate-drain charge	Q_{gd}		-	2.5	-	
DRAIN-SOURCE DIODE CHARACTERISTICS						
Diode forward voltage	V_{SD}	$V_{GS}=0V, I_S=2A$	-	0.76	1.16	V

Notes

- a. Pulse test: Pulse width $\leq 300 \mu s$, duty cycle $\leq 2\%$
- b. Guaranteed by design, not subject to production testing

»Package Information

SOT23-6L



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
θ	0°	8°	0°	8°

»Ordering information

Order code	Package	Marking	Base qty	Delivery mode
BM8205	SOT23-6L	8205	3K	Tape and reel