



NOTES:

- 1. INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 2. FERRULE & WASHER = BERYLLIUM COPPER PER ASTM B196, ALLOY C17300, TEMPER TD04.
 3. GASKET = SILICONE RUBBER PER MIL—R—5847.
- 4. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHER METAL PARTS = NICKEL PLATE PER AMS-QQ-N-290, CLASS 1, GRADE G, EXCEPT 100 TO 200µin THICK OVER 50 TO 100µin THICK COPPER PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: D.N. CHKD:	DATE 05/07/18 DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior RADIALL company written permission of RADIALL.				
· · · · · · · · · · · · · · · · · · ·		CITIND.	DATE	written permission of RADIALL.				
DECIMAL	ANGLE	C.E.	05/07/18	TNC STRAIGHT PLUG				
		APVD: DATE CLAMP TYPE					(
	J.M. 05/07/18 FOR RG-316 & SIMILAR				ABLES			
REFERENCE:		MATERIALS &	FINISHES:	SIZE	FSCM NO.	DWG NO.		REV
ORIGINATED: D.N. DATE: 05/07/18		SEE NOTES		A	19505	6000-7051	-003	А
				SCALE 4:1		THIRD ANGLE PROJECTION	SHEET 1 OF 1	