



## Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Plug	Plug - Elbow
Locking system	Push-pull
Matching parts	<a href="#">ERA.01.250.DLL</a>

## Technical details

### Electrical Configuration

Coax	1
Contact Termination Coax	Solder
Insert configuration value	1.25 - 1 Coax (50 Ohm)
Contact Type	Solder

### Form & Material

Shell style / Model id	FLS.01 - Elbow plug, for cable crimping
Plug	Elbow
Housing material	Brass (gold plated [ISO 27874]) shell, collet nut, brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular, male
Weight	2.28 g

[https://www.lemo.com/int\\_en/fls-01-250-dlae31.html](https://www.lemo.com/int_en/fls-01-250-dlae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


## Environment

Environmental protection	IP50
Minimal temperature	-55°C / +230°C

## Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Crimp

# Drawings



## Dimensions

	<b>A</b>	<b>L</b>	<b>H</b>	<b>M</b>
mm.	7.5	12.1	12	6.6
in.	0.3	0.48	0.47	0.26

[https://www.lemo.com/int\\_en/fls-01-250-dlae31.html](https://www.lemo.com/int_en/fls-01-250-dlae31.html)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.