
	70
	\setminus
	ά
	1
	\overline{G}
	/
	_
_	
) ('
	()
+	_



NOTES:

MATERIALS:

- 5. ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER MIL-G-45204, TYPE II, CLASS 1, GRADE C, OVER .00010 TO .00020 STRESS FREE SULFAMATE NICKEL PER QQ-N-290.

 2. SPRING = NICKEL PLATE PER QQ-N-290, CLASS 1, GRADE G,
- EXCEPT .0001 TO .0002 THICK OVER .00005 TO .0001 THICK COPPER PER MIL—C—14550.

 3. ALL OTHER METAL PARTS = GOLD PLATE PER MIL—G—45204, TYPE II, CLASS 0, GRADE C, OVER
 .00010 TO .00020 COPPER STRIKE PER MIL—C—14550.

	UNLESS OTHERWISE SPECIFIED		DWN:	DATE	Property of Radiall This document cannot be reproduced or				
	DIMENSIONS ARE IN	MENSIONS ARE IN INCHES		04/11/13					
Į	TOLERANCES O	N	CHKD:	DATE	communicated to a third party without prior a RADIALL company written permission of RADIALL.				
Į	DECIMAL	ANGLE	D.N.	04/11/13	SMB STRAIGHT PLUG				
			APVD:	DATE	BULKHEAD MOUNTED/CRIMP TYPE				
			J.M.	04/11/13	FOR RG-316 & SIMÍLAR CABLES				
Ī	REFERENCE:		MATERIALS & F	INISHES:	SIZE	FSCM NO.	DWG NO.	4 007	REV
	ORIGINATED: J.S.		SEE NOTES		Α	19505	2028-157	1-003	A
	DATE: 04/11/13				SCALE 5:1		THIRD ANGLE PROJECTION	SHEET 1 O	F 1