
APPROVED

D.N.



NOTES:

MATERIALS:

- INSULATORS = VIRGIN WHITE TEFLON PER ASTM D1710, GRADE 1, TYPE I, CLASS "B".
 CRIMP SLEEVE = SEAMLESS LOWLEAD BRASS TUBE, ALLOY 330, SOFT ANNEAL TEMPER, .025/.060 GRAIN SIZE OR SEAMLESS COPPER TUBE PER ASTM B75, TYPE C12000, TEMPER: LIGHT ANNEAL 050 EXCEPT YIELD STRENGTH.
 LOCKWASHER = PHOSPHOR BRONZE PER ASTM B139, COPPER ALLOY C53400, TEMPER H04.
 ALL OTHER METAL PARTS = BRASS PER ASTM B16, ALLOY C36000, TEMPER H02.

FINISHES:

- 1. CONTACT = GOLD PLATE PER ASTM B488-11, TYPE II, 50µin MIN, GRADE C, OVER 100 TO 200µin STRESS FREE SULFAMATE NICKEL PER AMS-QQ-N-290.

 2. ALL OTHER METAL PARTS = GOLD PLATE PER ASTM B488-11, TYPE II, 30µin MIN, GRADE C OVER 100 TO 200µin COPPER STRIKE PER AMS 2418.

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON		DWN: DATE D.N. 12/03/15 CHKD: DATE	Property of Radiall This document cannot be reproduced or communicated to a third party without prior RADIALL company written permission of RADIALL.			
DECIMAL	ANGLE	N.D. 12/03/15 APVD: DATE J.M. 12/03/15	<u> </u> 	SMB R	RIGHT ANGLE MALE JACK CRIMP TYPE -316DS & SIMILAR CABLES	
REFERENCE: ORIGINATED: D.N.	l	MATERIALS & FINISHES: SEE NOTES	size A	FSCM NO. 19505		rev A
DATE: 12/03/15			SCALE 5:1		THIRD ANGLE SHEET 1 OF	1