



50W 10-15GHZ 20DB DIRECTIONAL COUPLER

SERIES COUPLER PAGE 1/2 ISSUE **09-12-19A** PART NUMBER R433824000 **Scale 2:1** 48 max. 6,45 12,7 32 max. **RADIALL** -20dB R433.824.000 10-15 GHz 15 **Date Code** 6,6 1 Hole 2,2 9,5 \emptyset 2,6 13 (Typ. *) 25,6 RADIALL R433.824.000 -20dB 10-15 GHZ Date Code

All dimensions are in mm. Tolerances according ISO 2768 m-H

Weight Specification **26,9800** g







50W 10-15GHZ 20DB DIRECTIONAL COUPLER

PAGE 2 / 2	ISSUE 09-12-19A	SERIES COUPLER	PART NUMBER R433824000
--------------------------	------------------------	-------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency operating range:	10 – 15 GHz
Impedance:	50 Ω
VSWR: - Main Line	1.35 max.
- Coupled Line	1.35 max.
Nominal Coupling:	20 dB
Coupling Precision:	± 1 dB
Directivity:	15 dB mini
Insertion loss:	0.4 dB max.
Frequency Sensitivity:	± 0.5 dB
Average Power at 25°C	50W
Peak Power at 25°C	3000W

MECHANICAL CHARACTERISTICS

Connector type:	SMA female per MIL-C 39012
Coaxial Termination:	SMA, 50 Ω, 1W

ENVIRONMENTAL CHARACTERISTICS

Operating temperature :	-25°C / +85°C
Storage temperature :	-25°C / +85°C