




◆ Features:

- ◊ Fast switching speed
开关速度快
- ◊ High input impedance and low level drive
高输入阻抗和低电平驱动
- ◊ Avalanche energy tested
雪崩能量测试
- ◊ Improved dv/dt capability, high ruggedness
提高 dv/dt 能力，高耐用性

◆ Applications

- ◊ High efficiency switch mode power supplies
高效率开关电源
- ◊ Power factor correction
功率因数校正
- ◊ Electronic lamp ballast
电子整流器

 RoHS
COMPLIANT**TO-220F**



OSPF16N65

650V N-CHANNEL MOSFET

<http://www.osen.net.cn>

◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings		Unit
V _{DSS}	Drain-Source Voltage 漏源电压	650		V
V _{GS}	Gate-Source Voltage-Continuous 栅源电压	±30		V
I _D	Drain Current-Continuous (Note 2) 漏极持续电流	16		A
I _{DM}	Drain Current-Single Plused (Note 1) 漏极单次脉冲电流	64		A
P _D	Power Dissipation (Note 2) 功率损耗	62		W
T _j	Max.Operating junction temperature 最大结温	150		°C

◆ Electrical characteristics (Tc=25°C unless otherwise noted)

Symbol	Parameters	Min	Typ	Max	Units	Conditions
Static Characteristics						
B _{VDSS}	Drain-Source Breakdown VoltageCurrent (Note 1) 漏极击穿电压	650	--	--	V	I _D =250μA, V _{GS} =0V, T _j =25°C
V _{GS(th)}	Gate Threshold Voltage 栅极开启电压	2.0	--	4.0	V	V _{DS} =V _{GS} , I _D =250μA
R _{DS(on)}	Drain-Source On-Resistance 漏源导通电阻	--	0.52	--	Ω	V _{GS} =10V, I _D =8A
I _{GSS}	Gate-Body Leakage Current 栅极漏电流	--	--	±90	nA	V _{GS} =±30V, V _{DS} =0
I _{DSS}	Zero Gate Voltage Drain Current 零栅极电压漏极电流	--	--	200	nA	V _{DS} =650V, V _{GS} =0
g _{fS}	Forward Transconductance 正向跨导	--	6.0	--	S	V _{DS} =30V, I _D =8A



OSPF16N65

650V N-CHANNEL MOSFET

Switching Characteristics

$T_{d(on)}$	Turn-On Delay Time 开启延迟时间	--	16	--	ns	$V_{DS}=325V, I_D=16A,$ $R_G=25\Omega$ (Note 2)
T_r	Rise Time 上升时间	--	45	--	ns	
$T_{d(off)}$	Turn-Off Delay Time 关闭延迟时间	--	85	--	ns	
T_f	Fall Time 下降时间	--	18	--	ns	
Q_g	Total Gate Charge 栅极总电荷	--	55	--	nC	$V_{DS}=520V$, $V_{GS}=0-10V$, $I_D=16A$ (Note 2)
Q_{gs}	Gate-Source Charge 栅源极电荷	--	15	--	nC	
Q_{gd}	Gate-Drain Charge 栅漏极电荷	--	21	--	nC	

Dynamic Characteristics

C_{iss}	Input Capacitance 输入电容	--	2800	--	pF	$V_{DS}=25V, V_{GS}=0,$ $f=1MHz$
C_{oss}	Output Capacitance 输出电容	--	380	--	pF	
C_{rss}	Reverse Transfer Capacitance 反向传输电容	--	20	--	pF	
I_s	Continuous Drain-Source Diode Forward Current (Note 2) 二极管导通正向持续电流	--	--	16	A	
V_{SD}	Diode Forward On-Voltage 二极管正向导通电压	--	--	0.9	V	$I_s=1A, V_{GS}=0$
$R_{th(j-c)}$	Thermal Resistance, Junction to Case 结到外壳的热阻	--	--	2.02	°C/W	

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW <= 300us , duty cycle <= 2%.