

Thin-Film Directional Coupler

For 2400-2500MHz / 4900-5850MHz

TFSC06053925-2111B2X

0.65x0.5mm [EIA 0202]*

* Dimensions Code JIS[EIA]




Thin-Film Directional Coupler

For 2400-2500MHz / 4900-5850MHz

Conformity to RoHS Directive


TFSC06053925-2111B2X

SHAPES AND DIMENSIONS



Dimensions in mm

■ RECOMMENDED LAND PATTERN



Dimensions in mm

Line width be designed to match 50Ω characteristic impedance depending on PCB material and thickness.

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



TFSC06053925-2111B2X

ELECTRICAL CHARACTERISTICS

ltem	Frequency Range (MHz)	Min.	Тур.	Max.
Coupling Factor (dB)	2400 to 2500	20.5	21.8	22.5
	4900 to 5850	13.8	15.2	16.2
Insertion Loss (dB)	2400 to 2500	_	0.11	0.22
	4900 to 5850	_	0.22	0.32
Return Loss (dB)	2400 to 2500	17.69	50.0	_
	4900 to 5850	17.69	20.3	_
Directivity (dB)	2400 to 2500	16	19.4	_
	4900 to 5850	16	21.7	_
Power Handling (dBm)		_	_	35
Characteristic Impedance (Ω)			50 (Nominal)	

[•] Ta: +25°C±5°C

■TEMPERATURE RANGE

Operating temperature	Storage temperature		
(°C)	(°C)		
-40 to +85	-40 to +85		


All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.




TFSC06053925-2111B2X

■ FREQUENCY CHARACTERISTICS


□INSERTION LOSS




□COUPLING




□RETURN LOSS



□ISOLATION



DIRECTIVITY




[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



TFSC06053925-2111B2X

■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering Critical zone (T3 to T4) Peak			
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	T3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30sec max.

^{*}t3: Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

[•] Before using these products, be sure to request the delivery specifications.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.