

# 100314

## Low Power Quint Differential Line Receiver

### General Description

The 100314 is a monolithic quint differential line receiver with emitter-follower outputs. An internal reference supply ( $V_{BB}$ ) is available for single-ended reception. When used in single-ended operation the apparent input threshold of the true inputs is 25 mV to 30 mV higher (positive) than the threshold of the complementary inputs. Unlike other F100K ECL devices, the inputs do not have input pull-down resistors.


Active current sources provide common-mode rejection of 1.0V in either the positive or negative direction. A defined output state exists if both inverting and non-inverting inputs are at the same potential between  $V_{EE}$  and  $V_{CC}$ . The defined state is logic HIGH on the  $\bar{O}_a-\bar{O}_e$  outputs.

### Features

- 35% power reduction of the 100114
- 2000V ESD protection
- Pin/function compatible with 100114
- Voltage compensated operating range = -4.2V to -5.7V
- Available to MIL-STD-883
- Available to industrial grade temperature range

### Ordering Code:


### Logic Symbol



| Pin Names             | Description                |
|-----------------------|----------------------------|
| $D_a-D_e$             | Data Inputs                |
| $\bar{D}_a-\bar{D}_e$ | Inverting Data Inputs      |
| $O_a-O_e$             | Data Outputs               |
| $\bar{O}_a-\bar{O}_e$ | Complementary Data Outputs |


## Connection Diagrams

24-Pin DIP/SOIC




DS010260-2

28-Pin PCC



DS010260-4

24-Pin Quad Cerpak



DS010260-3

## Absolute Maximum Ratings (Note 1)

Above which the useful life may be impaired (Note 1)

|  |                   |
|--|-------------------|
| Storage Temperature ( $T_{STG}$ )        | -65°C to +150°C   |
| Maximum Junction Temperature ( $T_J$ )   |                   |
| Ceramic                                  | +175°C            |
| Plastic                                  | +150°C            |
| Pin Potential to Ground Pin ( $V_{EE}$ ) | -7.0V to +0.5V    |
| Input Voltage (DC)                       | $V_{EE}$ to +0.5V |
| Output Current (DC Output HIGH)          | -50 mA            |
| ESD (Note 2)                             | $\geq 2000V$      |

## Recommended Operating Conditions

|                             |                 |
|-----------------------------|-----------------|
| Case Temperature ( $T_C$ )  |                 |
| Commercial                  | 0°C to +85°C    |
| Industrial                  | -40°C to +85°C  |
| Military                    | -55°C to +125°C |
| Supply Voltage ( $V_{EE}$ ) | -5.7V to -4.2V  |

**Note 1:** Absolute maximum ratings are those values beyond which the device may be damaged or have its useful life impaired. Functional operation under these conditions is not implied.

**Note 2:** ESD testing conforms to MIL-STD-883, Method 3015.

## Commercial Version DC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$ ,  $T_C = 0^\circ C$  to  $+85^\circ C$  (Note 3)

| Symbol     | Parameter                          | Min            | Typ   | Max            | Units   | Conditions   |
|------------|------------------------------------|----------------|-------|----------------|---------|--|
| $V_{OH}$   | Output HIGH Voltage                | -1025          | -955  | -870           | mV      | $V_{IN} = V_{IH}$ (Max)<br>or $V_{IL}$ (Min)   |
| $V_{OL}$   | Output LOW Voltage                 | -1830          | -1705 | -1620          | mV      |  |
| $V_{OHC}$  | Output HIGH Voltage                | -1035          |       |                | mV      | $V_{IN} = V_{IH}$<br>or $V_{IL}$ (Max)   |
| $V_{OLC}$  | Output LOW Voltage                 |                |       | -1610          | mV      |  |
| $V_{BB}$   | Output Reference Voltage           | -1380          | -1320 | -1260          | mV      | $I_{V_{BB}} = -250 \mu A$  |
| $V_{DIFF}$ | Input Voltage Differential         | 150            |       |                | mV      | Required for Full Output Swing   |
| $V_{CM}$   | Common Mode Voltage                | $V_{CC} - 2.0$ |       | $V_{CC} - 0.5$ | V       |  |
| $V_{IH}$   | Single-Ended<br>Input High Voltage | -1110          |       | -870           | mV      | Guaranteed HIGH Signal for All<br>Inputs (with one input tied to $V_{BB}$ )<br>$V_{BB} (Max) + V_{DIFF}$ |
| $V_{IL}$   | Single-Ended<br>Input Low Voltage  | -1830          |       | -1530          | mV      | Guaranteed LOW Signal for All<br>Inputs (with one input tied to $V_{BB}$ )<br>$V_{BB} (Min) - V_{DIFF}$  |
| $I_{IL}$   | Input LOW Current                  | 0.50           |       |                | $\mu A$ | $V_{IN} = V_{IL} (Min)$  |
| $I_{IH}$   | Input HIGH Current                 |                |       | 240            | $\mu A$ | $V_{IN} = V_{IH} (Max)$ , $D_a - D_e = V_{BB}$ ,<br>$\overline{D}_a - \overline{D}_e = V_{IL} (Min)$     |
| $I_{CBO}$  | Input Leakage Current              | -10            |       |                | $\mu A$ | $V_{IN} = V_{EE}$ , $D_a - D_e = V_{BB}$ ,<br>$\overline{D}_a - \overline{D}_e = V_{IL} (Min)$           |
| $I_{EE}$   | Power Supply Current               | -60            |       | -30            | mA      | $D_a - D_e = V_{BB}$ , $\overline{D}_a - \overline{D}_e = V_{IL} (Min)$                                  |

**Note 3:** The specified limits represent the "worst case" value for the parameter. Since these values normally occur at the temperature extremes, additional noise immunity and guardbanding can be achieved by decreasing the allowable system operating ranges. Conditions for testing shown in the tables are chosen to guarantee operation under "worst case" conditions.

## DIP AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol                 | Parameter                                 | $T_C = 0^\circ C$ |      | $T_C = +25^\circ C$ |      | $T_C = +85^\circ C$ |      | Units | Conditions   |
|------------------------|---|-------------------|------|---------------------|------|---------------------|------|-------|--------------|
|                        |   | Min               | Max  | Min                 | Max  | Min                 | Max  |       |              |
| $f_{MAXFS}$            | Toggle Frequency<br>(Full Swing)          | 250               |      | 250                 |      | 250                 |      | MHz   | (Note 2)     |
| $f_{MAXRS}$            | Toggle Frequency<br>(Reduced Swing)       | 700               |      | 700                 |      | 700                 |      | MHz   | (Note 3)     |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation Delay<br>Data to Output       | 0.65              | 1.90 | 0.65                | 2.00 | 0.70                | 2.00 | ns    | Figures 1, 2 |
| $t_{TLH}$<br>$t_{THL}$ | Transition Time<br>20% to 80%, 80% to 20% | 0.35              | 1.20 | 0.35                | 1.20 | 0.35                | 1.20 | ns    |              |

## SOIC, PCC and Cerpak AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol                 | Parameter   | $T_C = 0^\circ C$ |      | $T_C = +25^\circ C$ |      | $T_C = +85^\circ C$ |      | Units | Conditions               |
|------------------------|---|-------------------|------|---------------------|------|---------------------|------|-------|--------------------------|
|                        |   | Min               | Max  | Min                 | Max  | Min                 | Max  |       |                          |
| $f_{MAXFS}$            | Toggle Frequency<br>(Full Swing)  | 250               |      | 250                 |      | 250                 |      | MHz   | (Note 5)                 |
| $f_{MAXRS}$            | Toggle Frequency<br>(Reduced Swing)   | 700               |      | 700                 |      | 700                 |      | MHz   | (Note 6)                 |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation Delay<br>Data to Output   | 0.65              | 1.70 | 0.65                | 1.80 | 0.70                | 1.80 | ns    | Figures 1, 2             |
| $t_{TLH}$<br>$t_{THL}$ | Transition Time<br>20% to 80%, 80% to 20%                                       | 0.35              | 1.10 | 0.35                | 1.10 | 0.35                | 1.10 | ns    |                          |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation Delay<br>Data to Output   | 0.70              | 1.50 | 0.80                | 1.60 | 0.90                | 1.80 | ns    | PCC only                 |
| $t_{OSHL}$             | Maximum Skew Common Edge<br>Output-to-Output Variation<br>Data to Output Path   | 280               |      | 280                 |      | 280                 |      | ps    | PCC only<br>(Notes 4, 7) |
| $t_{OSLH}$             | Maximum Skew Common Edge<br>Output-to-Output Variation<br>Data to Output Path   | 330               |      | 330                 |      | 330                 |      | ps    | PCC only<br>(Notes 4, 7) |
| $t_{OST}$              | Maximum Skew Opposite Edge<br>Output-to-Output Variation<br>Data to Output Path | 330               |      | 330                 |      | 330                 |      | ps    | PCC only<br>(Notes 4, 7) |
| $t_{PS}$               | Maximum Skew<br>Pin (Signal) Transition Variation<br>Data to Output Path        | 320               |      | 320                 |      | 320                 |      | ps    | PCC only<br>(Notes 4, 7) |

**Note 4:** Output-to-Output Skew is defined as the absolute value of the difference between the actual propagation delay for any outputs within the same packaged device. The specifications apply to any outputs switching in the same direction either HIGH to LOW ( $t_{OSHL}$ ), or LOW to HIGH ( $t_{OSLH}$ ), or in opposite directions both HL and LH ( $t_{OST}$ ). Parameters  $t_{OST}$  and  $t_{PS}$  guaranteed by design.

**Note 5:** Maximum toggle frequency at which  $V_{OH}$  and  $V_{OL}$  DC specifications are maintained.

**Note 6:** Maximum toggle frequency at which outputs maintain 150 mV swing.

**Note 7:** All skews calculated using input crossing point to output crossing point propagation delays.

## Industrial Version PCC DC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$ ,  $T_C = -40^{\circ}C$  to  $+85^{\circ}C$  (Note 8)

| Symbol     | Parameter                       | $T_C = -40^{\circ}C$ |                | $T_C = 0^{\circ}C$ to $+85^{\circ}C$ |                | Units   | Conditions   |                                    |
|------------|---------------------------------|----------------------|----------------|--------------------------------------|----------------|---------|--|------------------------------------|
|            |                                 | Min                  | Max            | Min                                  | Max            |         |  |                                    |
| $V_{OH}$   | Output HIGH Voltage             | -1085                | -870           | -1025                                | -870           | mV      | $V_{IN} = V_{IH}$ (Max)  | Loading with $50\Omega$ to $-2.0V$ |
| $V_{OL}$   | Output LOW Voltage              | -1830                | -1575          | -1830                                | -1620          | mV      | or $V_{IL}$ (Min)  |                                    |
| $V_{OHC}$  | Output HIGH Voltage             | -1095                |                | -1035                                |                | mV      | $V_{IN} = V_{IH}$  | Loading with $50\Omega$ to $-2.0V$ |
| $V_{OLC}$  | Output LOW Voltage              |                      | -1565          |                                      | -1610          | mV      | or $V_{IL}$ (Min)  |                                    |
| $V_{BB}$   | Output Reference Voltage        | -1395                | -1255          | -1380                                | -1260          | mV      | $I_{V_{BB}} = -250 \mu A$  |                                    |
| $V_{DIFF}$ | Input Voltage Differential      | 150                  |                | 150                                  |                | mV      | Required for Full Output Swing   |                                    |
| $V_{CM}$   | Common Mode Voltage             | $V_{CC} - 2.0$       | $V_{CC} - 0.5$ | $V_{CC} - 2.0$                       | $V_{CC} - 0.5$ | V       |  |                                    |
| $V_{IH}$   | Single-Ended Input High Voltage | -1115                | -870           | -1110                                | -870           | mV      | Guaranteed HIGH Signal for All Inputs (with one input tied to $V_{BB}$ ) $V_{BB} (Max) + V_{DIFF}$ |                                    |
| $V_{IL}$   | Single-Ended Input Low Voltage  | -1830                | -1535          | -1830                                | -1530          | mV      | Guaranteed LOW Signal for All Inputs (with one input tied to $V_{BB}$ ) $V_{BB} (Min) - V_{DIFF}$  |                                    |
| $I_{IL}$   | Input LOW Current               | 0.50                 |                | 0.50                                 |                | $\mu A$ | $V_{IN} = V_{IL} (Min)$  |                                    |
| $I_{IH}$   | Input HIGH Current              | 240                  |                | 240                                  |                | $\mu A$ | $V_{IN} = V_{IH} (Max)$ , $D_a - D_e = V_{BB}$ , $\overline{D}_a - \overline{D}_e = V_{IL} (Min)$  |                                    |
| $I_{CBO}$  | Input Leakage Current           | -10                  |                | -10                                  |                | $\mu A$ | $V_{IN} = V_{EE}$ , $D_a - D_e = V_{BB}$ , $\overline{D}_a - \overline{D}_e = V_{IL} (Min)$        |                                    |
| $I_{EE}$   | Power Supply Current            | -60                  | -30            | -60                                  | -30            | mA      | $D_a - D_e = V_{BB}$ , $\overline{D}_a - \overline{D}_e = V_{IL} (Min)$                            |                                    |

**Note 8:** The specified limits represent the "worst case" value for the parameter. Since these values normally occur at the temperature extremes, additional noise immunity and guardbanding can be achieved by decreasing the allowable system operating ranges. Conditions for testing shown in the tables are chosen to guarantee operation under "worst case" conditions.

## PCC AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol      | Parameter                              | $T_C = -40^{\circ}C$ |      | $T_C = +25^{\circ}C$ |      | $T_C = +85^{\circ}C$ |      | Units | Conditions   |
|-------------|--|----------------------|------|----------------------|------|----------------------|------|-------|--------------|
|             |  | Min                  | Max  | Min                  | Max  | Min                  | Max  |       |              |
| $f_{MAXFS}$ | Toggle Frequency (Full Swing)          | 250                  |      | 250                  |      | 250                  |      | MHz   | (Note 5)     |
| $f_{MAXRS}$ | Toggle Frequency (Reduced Swing)       | 700                  |      | 700                  |      | 700                  |      | MHz   | (Note 6)     |
| $t_{PLH}$   | Propagation Delay Data to Output       | 0.65                 | 1.70 | 0.65                 | 1.80 | 0.70                 | 1.80 | ns    | Figures 1, 2 |
| $t_{TLH}$   | Transition Time 20% to 80%, 80% to 20% | 0.20                 | 1.40 | 0.35                 | 1.10 | 0.35                 | 1.10 | ns    |              |
| $t_{PHL}$   |  |                      |      |                      |      |                      |      |       |              |
| $t_{THL}$   |  |                      |      |                      |      |                      |      |       |              |

## Military Version DC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$ ,  $T_C = -55^\circ C$  to  $+125^\circ C$  (Note 11)

| Symbol     | Parameter                       | Min            | Typ | Max            | Units   | $T_C$                           | Conditions   | Notes                 |
|------------|---------------------------------|----------------|-----|----------------|---------|---------------------------------|--|-----------------------|
| $V_{OH}$   | Output HIGH Voltage             | -1025          |     | -870           | mV      | $0^\circ C$ to $+125^\circ C$   | $V_{IN} = V_{IH} (Max)$<br>or $V_{IL} (Min)$<br><br>Loading with $50\Omega$ to $-2.0V$               | (Notes 9, 10, 11)     |
|            |                                 | -1085          |     | -870           | mV      | $-55^\circ C$                   |  |                       |
| $V_{OL}$   | Output LOW Voltage              | -1830          |     | -1620          | mV      | $0^\circ C$ to $+125^\circ C$   |  |                       |
|            |                                 | -1830          |     | -1555          | mV      | $-55^\circ C$                   |  |                       |
| $V_{OHC}$  | Output HIGH Voltage             | -1035          |     |                | mV      | $0^\circ C$ to $+125^\circ C$   | $V_{IN} = V_{IH} (Max)$<br>or $V_{IL} (Min)$<br><br>Loading with $50\Omega$ to $-2.0V$               | (Notes 9, 10, 11)     |
|            |                                 | -1085          |     |                | mV      | $-55^\circ C$                   |  |                       |
| $V_{OLC}$  | Output LOW Voltage              |                |     | -1610          | mV      | $0^\circ C$ to $+125^\circ C$   |  |                       |
|            |                                 |                |     | -1555          | mV      | $-55^\circ C$                   |  |                       |
| $V_{BB}$   | Output Reference Voltage        |                |     | -1260          | mV      | $0^\circ C$ to $+125^\circ C$   | $I_{VBB} = 0 \mu A$ , $V_{EE} = 4.2V$  | (Notes 9, 10, 11)     |
|            |                                 | -1380          |     | -1260          | mV      | $0^\circ C$ to $+125^\circ C$   | $I_{VBB} = -250 \mu A$ , $V_{EE} = -5.7V$  | (Notes 9, 10, 11)     |
|            |                                 | -1396          |     |                | mV      | $-55^\circ C$                   | $I_{VBB} = -350 \mu A$ , $V_{EE} = -5.7V$  |                       |
| $V_{DIFF}$ | Input Voltage Differential      | 150            |     |                | mV      | $-55^\circ C$ to $+125^\circ C$ | Required for Full Output Swing   | (Notes 9, 10, 11)     |
| $V_{CM}$   | Common Mode Voltage             | $V_{CC} - 2.0$ |     | $V_{CC} - 0.5$ | V       | $-55^\circ C$ to $+125^\circ C$ |  | (Notes 9, 10, 11)     |
| $V_{IH}$   | Single-Ended Input High Voltage | -1165          |     | -870           | mV      | $-55^\circ C$ to $+125^\circ C$ | Guaranteed HIGH Signal for All Inputs (with $\overline{D}_n$ tied to $V_{BB}$ )                      | (Notes 9, 10, 11, 12) |
| $V_{IL}$   | Single-Ended Input Low Voltage  | -1830          |     | -1475          | mV      | $-55^\circ C$ to $+125^\circ C$ | Guaranteed LOW Signal for All Inputs (with $\overline{D}_n$ tied to $V_{BB}$ )                       | (Notes 9, 10, 11, 12) |
| $I_{IH}$   | Input HIGH Current              |                |     | 50             | $\mu A$ | $0^\circ C$ to $+125^\circ C$   | $V_{IN} = V_{IH} (Max)$ , $D_a - D_e = V_{BB}$ ,<br>$\overline{D}_a - \overline{D}_e = V_{IL} (Min)$ | (Notes 9, 10, 11)     |
|            |                                 |                |     | 70             | $\mu A$ | $-55^\circ C$                   |  |                       |
| $I_{CBO}$  | Input Leakage Current           | -10            |     |                | $\mu A$ | $-55^\circ C$ to $+125^\circ C$ | $V_{IN} = V_{EE}$ , $D_a - D_e = V_{BB}$ ,<br>$\overline{D}_a - \overline{D}_e = V_{IL} (Min)$       | (Notes 9, 10, 11)     |
| $I_{EE}$   | Power Supply Current            | -65            |     | -25            | mA      | $-55^\circ C$ to $+125^\circ C$ | $D_a - D_e = V_{BB}$ ,<br>$\overline{D}_a - \overline{D}_e = V_{IL} (Min)$                           | (Notes 9, 10, 11)     |

**Note 9:** F100K 300 Series cold temperature testing is performed by temperature soaking (to guarantee junction temperature equals  $-55^\circ C$ ), then testing immediately without allowing for the junction temperature to stabilize due to heat dissipation after power-up. This provides "cold start" specs which can be considered a worst case condition at cold temperatures.

**Note 10:** Screen tested 100% on each device at  $-55^\circ C$ ,  $+25^\circ C$ , and  $+125^\circ C$ , Subgroups 1, 2, 3, 7, and 8.

**Note 11:** Sample tested (Method 5005, Table I) on each manufactured lot at  $-55^\circ C$ ,  $+25^\circ C$ , and  $+125^\circ C$ , Subgroups A1, 2, 3, 7, and 8.

**Note 12:** Guaranteed by applying specified input condition and testing  $V_{OH}/V_{OL}$ .

## AC Electrical Characteristics

$V_{EE} = -4.2V$  to  $-5.7V$ ,  $V_{CC} = V_{CCA} = GND$

| Symbol    | Parameter              | $T_C = -55^\circ C$ |      | $T_C = +25^\circ C$ |      | $T_C = +125^\circ C$ |      | Units | Conditions   | Notes              |
|-----------|------------------------|---------------------|------|---------------------|------|----------------------|------|-------|--------------|--------------------|
|           |                        | Min                 | Max  | Min                 | Max  | Min                  | Max  |       |              |                    |
| $t_{PLH}$ | Propagation Delay      | 0.40                | 2.30 | 0.60                | 2.20 | 0.60                 | 2.70 | ns    | Figures 1, 2 | (Notes 13, 14, 15) |
| $t_{PHL}$ | Data to Output         |                     |      |                     |      |                      |      |       |              |                    |
| $t_{TLH}$ | Transition Time        | 0.20                | 1.40 | 0.20                | 1.40 | 0.20                 | 1.40 | ns    |              | (Note 16)          |
| $t_{THL}$ | 20% to 80%, 80% to 20% |                     |      |                     |      |                      |      |       |              |                    |


**Note 13:** F100K 300 Series cold temperature testing is performed by temperature soaking (to guarantee junction temperature equals  $-55^\circ C$ ), then testing immediately after power-up. This provides "cold start" specs which can be considered a worst case condition at cold temperatures.

**Note 14:** Screen tested 100% on each device at  $+25^\circ C$  temperature only, Subgroup A9.

**Note 15:** Sample tested (Method 5005, Table I) on each manufactured lot at  $+25^\circ C$ , Subgroup A9, and at  $+125^\circ C$  and  $-55^\circ C$  temperatures, Subgroups A10 and A11.

**Note 16:** Not tested at  $+25^\circ C$ ,  $+125^\circ C$  and  $-55^\circ C$  temperature (design characterization data).

## Test Circuit




DS010260-5

**Note:**  $V_{CC}$ ,  $V_{CCA} = +2V$ ,  $V_{EE} = -2.5V$   
 $L1$  and  $L2 =$  equal length  $50\Omega$  impedance lines  
 $R_T = 50\Omega$  terminator internal to scope  
 Decoupling  $0.1 \mu F$  from GND to  $V_{CC}$  and  $V_{EE}$   
 All unused outputs are loaded with  $50\Omega$  to GND  
 $C_L =$  Fixture and stray capacitance  $\leq 3 pF$

FIGURE 1. AC Test Circuit

## Switching Waveforms




DS010260-6

FIGURE 2. Propagation Delay and Transition Times

## Ordering Information


The device number is used to form part of a simplified purchasing code where a package type and temperature range are defined as follows:




DS010260-7



**Physical Dimensions** inches (millimeters) unless otherwise noted




**24-Lead Ceramic Dual-In-Line Package (0.400" Wide) (D)  
Package Number J24E**



**24-Lead Molded Package (0.300" Wide) (S)  
Package Number M24B**


**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)



**24-Lead Plastic Dual-In-Line Package (P)**  
**Package Number N24E**

N24E (REV A)


**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)



**28-Lead Plastic Chip Carrier (Q)**  
**Package Number V28A**

V28A (REV K1)

**Physical Dimensions** inches (millimeters) unless otherwise noted (Continued)



W24B (REV D)

**24-Lead Quad Cerpak (F)  
Package Number W24B**

**LIFE SUPPORT POLICY**

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Fairchild Semiconductor Corporation  
Americas  
Customer Response Center  
Tel: 1-888-522-5372

Fairchild Semiconductor Europe  
Fax: +49 (0) 1 80-530 85 86  
Email: europe.support@nsc.com  
Deutsch Tel: +49 (0) 8 141-35-0  
English Tel: +44 (0) 1 793-85-68-56  
Italy Tel: +39 (0) 2 57 5631

Fairchild Semiconductor Hong Kong Ltd.  
13th Floor, Straight Block,  
Ocean Centre, 5 Canton Rd.  
Tsimshatsui, Kowloon  
Hong Kong  
Tel: +852 2737-7200  
Fax: +852 2314-0061

National Semiconductor Japan Ltd.  
Tel: 81-3-5620-6175  
Fax: 81-3-5620-6179

www.fairchildsemi.com