





SPECIFICATIONS

Current Rating: 3Amps
 Insulation Resistance: 1000MΩ Min
 Contact Resistance: 20mΩ Max
 Withstanding Voltage: AC 1000V
 Operation Temperature: -40°to+105°
 Contact Material: Brass
 Insulator Material: Polyester(UL 94V-0)
 Contact plating: Gold Flash
 Standard: PBT
 Max.Processing Temp: 200°C for30-60seconds
 (220°C for5seconds)

P/N	PIN	DIM.A	DIM.B
2.54DC2-01-06PZS	6	5.08	26.92
2.54DC2-01-08PZS	8	7.62	29.46
2.54DC2-01-10PZS	10	10.16	32.00
2.54DC2-01-12PZS	12	12.70	34.54
2.54DC2-01-14PZS	14	15.24	37.08
2.54DC2-01-16PZS	16	17.78	39.60
2.54DC2-01-20PZS	20	22.86	44.70
2.54DC2-01-24PZS	24	27.94	49.78
2.54DC2-01-26PZS	26	30.48	52.30
2.54DC2-01-30PZS	30	35.56	57.40
2.54DC2-01-34PZS	34	40.64	62.50
2.54DC2-01-40PZS	40	48.26	70.10
2.54DC2-01-50PZS	50	60.96	82.85
2.54DC2-01-60PZS	60	73.66	95.40
2.54DC2-01-64PZS	64	78.74	100.48



PART NUMBER DESCRIPTION:

2.54DC2-01-NPZS

(D=单排;S=双排)
 (Z=直脚;W=弯脚)
 (PIN数量;06.....64PIN)
 (排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE:2.54DC2-NPIn H17 180度 PC3.8 PBT
			PAR 2.54DC2-01-NPZS
DECIMALS:	ANGLES:	DWN	
X.±0.30	X°±5'	CHKD	
X.X±0.25	X.X°±1'	APVD	
X.XX±0.20	X.XX°±0.5'	SCALE N:A	UNIT:MM
CUSTOMER COPY		SIZE:A4	SHEET:1F1
			REV:A