
BIAS DRIVER

MECL MC300 series

MC304

Bias driver that compensates for changes in circuit parameters with temperature.



ELECTRICAL CHARACTERISTICS

	Test Conditions Vdc ± 1%										
@ Test { +25°c + 125°c	-5.20										
Characteristic	V _{ee}	į,	Ground	Symbol Pin No		55°C	Test Limits +25°C		+1	+125°C	
Power Supply Brain Correct	Pin No	Pia No	Pin No	in()	Min	Max	Min	Max	Min	Max	Vnit
Output Voltage				10 (2)	!	4.4	L <u>–</u>	4.4		4.0	mAdc
		10		Vae	-1.19	-1.32	-1.00	-1.22	-0.95	-1.08	Vdc

Pins not listed are left open.

1 Current test conditions; no load = 0; full load = -2.5 mAdc ±5%.

- CIRCUIT DESCRIPTION

Circuit Operation:

The divider network R₁, R₂, D₁, D₂ compensates for temperature variations of the base-emitter voltages of Q₁, and of the driven gates, producing a bias voltage for the MECL logic circuits that maintains a constant set of dc operating conditions over the temperature range of -55 to +125°C. In addition, compensation for power supply variations is achieved, since the bias output voltage is derived from the system supply.

Either of the supply voltage nodes may be used as ground, however the ground potential of the bias driver must coincide with that of the logic system. Thus, if Vcc is grounded in the logic system, then -

 $V_{CC} = 0;$ $V_{EE} = -5.2 \text{ V};$ $V_{RR} = -1.15$ nominal output voltage at 25°C